**Part Number :** 2177901124
**Product Description :** Pre-Crimped Lead Squba 1.8 Female-to-Squba 1.8 Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black
**Series Number :** 217790
**Status :** Active
**Product Category :** Power and Signal Cable Assemblies



## Documents and Resources

### Drawings

2177901124_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 217790 |
| Description | Pre-Crimped Lead Squba 1.8 Female-to-Squba 1.8 Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black |
| Application | Wire-to-Wire |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | Squba 1.8 Terminal-to-Squba 1.8 Terminal |
| Keyword | Squba 1.8 |
| Product Name | Squba |
| UPC | 195842123809 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 6.0A |
| Voltage - Maximum | 125V |

### Physical

| | |
|---|---|
| Cable Length | 300.00mm |
| Circuits (Loaded) | 1 |
| Circuits (maximum) | 1 |
| Color - Resin | Black |
| Gender | Female-Female |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Resin | PVC |
| Net Weight | 1.452/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.80mm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 10002 |
| Wire Size (AWG) | 22 |



Downloaded from Arrow.com.