



Color: ■ gray

Physical data	
Width	0.7 mm / 0.028 inches
Height	48.1 mm / 1.894 inches
Depth	28.9 mm / 1.138 inches

Mechanical data	
Mounting type	snap-on type

Material data	
Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.031 MJ
Weight	1.1 g

Environmental requirements			
Environmental Testing		Environmental Testing	
Test specification: Railway applications – Rolling stock – Electronic equipment	DIN EN 50155 (VDE 0115-200):2022-06	Test duration per axis	10 min.
Test procedure: Railway applications – Rolling stock equipment – Vibration and shock tests	DIN EN 61373 (VDE 0115-0106):2011-04	Test directions	X, Y and Z axes
Spectrum/Mounting location	Service life test, Category 1, Class A/B	Monitoring of contact faults and interrup- tions	Passed
Functional test with noise-like oscillations	Test passed according to Section 8 of the standard	Voltage drop measurement before and after each axis	Passed
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz	Simulated service life test through in- creased levels of noise-like oscillations	Test passed according to Section 9 of the standard
Acceleration	0.101g (highest test level used for all axes)	Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz
		Acceleration	0.572g (highest test level used for all axes)
		Test duration per axis	5 h



Environmental Testing	
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Shock test	Test passed according to Section 10 of the standard
Shock pulse form	Half sine
Acceleration	5g (highest test level used for all axes)
Shock duration	30 ms
Number of shocks (per axis)	3 pos. und 3 neg.
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Vibration and shock stress for rolling stock equipment	Passed

Commercial data		
Product Group	22 (TOPJOB S)	
PU (SPU)	100 (25) pcs	
Packaging type	Box	
Country of origin	CN	
GTIN	4045454711344	
Customs tariff number	85389099990	

Product Classification		
UNSPSC	39121702	
eCl@ss 10.0	27-14-11-33	
eCl@ss 9.0	27-14-11-33	
ETIM 9.0	EC000886	
ETIM 10.0	EC000886	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant, No Exemption	

Approvals / Certificates

Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready



Downloads			
Environmental Product Compliance			
Compliance Search			
Environmental Product Compliance 2000-1291			↓

Documentation			
Bid Text			
2000-1291	19.02.2019	xml 2.51 KB	↓
2000-1291	27.04.2017	doc 23.00 KB	↓

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 2000-1291	EPLAN Data Portal 2000-1291
↓	↓
	WSCAD Universe 2000-1291
	↓
	ZUKEN Portal 2000-1291
	↓