





PRODUCT NUMBER	PITCH
EQxx05x000J0G	5.00 mm



SECTION A-A

Material

- Item(a) Terminal cover : Thermoplastic (UL94V-0)
- Item(b) Terminal housing : Thermoplastic (UL94V-0)
- Item(c) Terminal screw : Steel Zinc plating "-" slot type
- Item(d) Solder pin : Brass, Tin plated
- Item(e) Clamp : Steel stamping, Zinc plating

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

PART NO.: EQ xx 0 5 x 0 00J0 G

DIMENSION

Dim L	Nx5.0
Dim B	(N-1)x5.0

N=Number of poles

Poles	DimL&B Tolerance
2P-6P	±0.15
7P-12P	±0.20
13P-18P	±0.25
19P-24P	±0.30

Solid block
No. of poles
02 2 poles
03 3 poles
...
24 24 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK			
					angles	X.±0.5	 title TERMINAL BLOCK RISING CLAMP, 90D WIRE INLET,SOLID BLOCK			
					parallel	X.X±0.3				
					X°±1°	X.XX±0.1	scale 			
					dr	EVIN ZHONG 041014	dwg no			
					enrg	EVIN ZHONG 041014	sheet 1 of 1 size			
					chr	HANKE FENG 041014	EQxx05x000J0G			
					appd	SHI JUN 041014	A4			
sheet index				revision	A		type			
				sheet	1		CUSTOMER Drawing			