



TP1410BF, Vinyl Block Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP1410BF](#)



Vinyl Block Fork Terminal For 16 - 14 AWG

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - Z inch	0.30 in
Dimension - L Length Overall mm	24 mm
Dimension - Pad Width inch	0.32 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	#8 - #10
Cable Insulation Diameter Maximum	0.180 in
Dimension - Length Overall inch	0.95 in

General

Sub Brand	HYDENT
Insulation Type	Vinyl
Physical Attribute - Tongue Type	Block Fork
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation Type	Y
Type	Fork Tongue
UPC 12 Digit	781810524336
UPC 14 Digit GTIN	00781810524336
Material	Copper
Plating Type	Tin
UPC	781810524336

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)