





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J3	SUPERSEDED 364175-E	23JUL2026	SA	LET

TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS





	SUPERSEDED	OBSOLETE			
-	-	1	-	TOP COVER	8
-	-	1	-	TRAY PACKAGING	7
1	1	-	-	TAPE & REEL	6
1	-	-	-	PAD	5
1	1	1	-	SOLDER CLIP LEFT	4
1	1	1	-	SOLDER CLIP RIGHT	3
4	4	4	-	PINS	2
1	1	1	-	HOUSING	1
474665-E	364175-E	454466-E	REV	DESCRIPTION	ITEM NO.
-	-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY			PARTS LIST		

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B S ADRUSH CHK M SZELAG APVD J DE BRUIJN PRODUCT SPEC	11AUG2023 13AUG2023 13AUG2023	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015	NAME M12 FEMALE, D CODE, 4P, 17MM SMT V		
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		± ± ± ± ± ±	108-94887 APPLICATION SPEC 114-94781 WEIGHT	SIZE A2	CAGE CODE 00779
MATERIAL -		FINISH -	114-94781 WEIGHT -	DRAWING NO C=454466-E	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV J3

PCB-LAYOUT PROPOSAL



3D VIEW
SCALE 2:1

- DRAWING SPECIFICATION ACCORDING TO DOCUMENT 5_3_16-DOC-1806-00915
- COPLANARITY OF ALL CLIPS ≤ 0,1MM

INSPECTION LEVEL 1: CONTROL CHART REQUIRED
1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
2) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

3) PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3