

Data Sheet

LL01CR-ABGxxL02


Xlamp MT-G


■ Features& Typical Applications

- High efficiency
- Available in 3 beam Patterns
- Optimized for uniform effects
- Lens without Housing
- Decorative Light
- Architectural Lighting
- Down Light

■ Table of Contents


General Information & Product Nomenclature.....	P.2
Optical Specifications	P.3
Mechanical Specifications	P.4
Package Specifications	P.5

LL01CR-ABGxxL02

General Information

- Lens Material Optical Grade PC
- Operating Temperature range -40°C~+110°C(upper limit +120°C)
- Storage Temperature range -40°C~+110°C(upper limit +120°C)
 - * Average transmittance in visible spectrum 400nm~700nm>90%
- Usage and Maintenance:
 1. If necessary, clean lenses with mild soap, water and soft cloth.
 2. Never use any commercial cleaning solvents on lenses, like alcohol.
 3. Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Product Nomenclature



LL01CR-ABGxxL02









Optical Specifications



Xlamp MT-G



Note: (1) degree: tolerance $\pm 2^\circ$
(2) optical value: tolerance $\pm 10\%$

Part Number	FWHM	Field Angle*	cd / lm	IES File
LL01CR-ABG24L02	25°	50°	3.1	Download
				
Beam Pattern	Light Distribution Curve	Illuminance Distribution		
Part Number	FWHM	Field Angle*	cd / lm	IES File
LL01CR-ABG38L02	41°	71°	1.8	Download
				
Beam Pattern	Light Distribution Curve	Illuminance Distribution		
Part Number	FWHM	Field Angle*	cd / lm	IES File
LL01CR-ABG55L02	59°	88°	1.1	Download
				
Beam Pattern	Light Distribution Curve	Illuminance Distribution		

*The Field Angle is the angle between the two directions opposed to each other over the beam axis for which the luminous intensity is 10% that of the maximum luminous intensity.
*This testing result is obtained through testing the popular rank LED samples which provided by the original manufacturer. Hence, the testing results would be varied as the users choose same LED model but different rank.

LL01CR-ABGxxL02

Mechanical Specification

1. Fixing method

Note: All dimensions are in mm.

☐ Glue


☐ Screw

☐ Tape


☒ Fixing-ring

☐ Frame

2. Lens dimensions




3. Lens + Leds+MCPCB assembly instruction



4. Lens assembly dimensions


5. View assembly lens with MCPCB:





LL01CR-ABGxxL02

Package Specifications

Item	Quantity	Total	Size(L*W*H)	G.W
Inner box		63 pcs	33*30*2.1 cm	5.7g
Outer box	567 pcs/box	567 pcs	35*31*21cm	
Outer box				



63pcs/ box



567pcs/inner box



Note: