



Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Number of Positions: 2  
Primary Product Color: **Black**  
Connector & Contact Retention Accessory Type: **Retainer**  
Primary Product Material: **PBT GF10**  
Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

|  |          |
|--|----------|
| Sealable                                     | No       |
| Connector & Contact Retention Accessory Type | Retainer |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 2 |
|---------------------|---|

Body Features

|                          |          |
|--------------------------|----------|
| Primary Product Color    | Black    |
| Primary Product Material | PBT GF10 |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 120 °C[-40 – 248 °F] |
|-----------------------------|----------------------------|

Industry Standards

|                        |         |
|------------------------|---------|
| UL Flammability Rating | UL 94HB |
|------------------------|---------|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Method   | Box  |
| Packaging Quantity | 6000 |

Other

|             |     |
|-------------|-----|
| Serviceable | Yes |
|-------------|-----|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free  |
| Solder Process Capability                     | Not applicable for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1587987-3  
RECEPTACLE ASSEMBLY, 250A, MSD



TE Part # 2315855-6  
MSD, REC HSG ASSY, 630A, V0, M8



TE Part # CAT-M8793-CH8172  
MQS, CONNECTOR HOUSING



TE Part # 1-1587987-4  
FUSE, RECEPTACLE ASSEMBLY, 630A, MSD



TE Part # 1299428-1  
CABLE ASSY-LV HVIL EXTN(ASM-001748)



TE Part # 2315855-4  
MSD, REC HSG ASSY, 450A, V0, M8

Customers Also Bought



TE Part #CAT-M8793-CH8172  
MQS, CONNECTOR HOUSING

TE Part #8-963964-4  
ACTION PIN FOR 1 mm HOLE

TE Part #1355390-1  
JUN-POW-TIM GEH 2P

TE Part #6-1355688-7  
MT3-REC. HOUSING, 6 POS.

TE Part #1587987-9  
RECEPTACLE ASSEMBLY, 250A, MSD

TE Part #1-1587987-1  
RECEPTACLE ASSEMBLY, 350A, MSD

TE Part #1-1587987-7  
RECEPTACLE ASSEMBLY, Shunt, MSD

TE Part #2103172-9  
Plug Assembly, 250A, MSD

TE Part #1-2103172-7  
Plug Assembly, Shunt, MSD

Documents

Product Drawings  
MQS RETAINER FOR 2POS REC.HSG  
English

CAD Files  
Customer View Model  
ENG\_CVM\_CVM\_1534112-1\_B.2d\_dxf.zip  
English  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_1534112-1\_B.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_1534112-1\_B.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

1534112-1

2 Position, Black, Retainer, PBT GF10, -40 – 120 °C [-40 – 248 °F]



Product Specification

English