



Size
Range

40 x 40 x 20 mm
BDC AXIAL FAN

1,57 x 1,57 x 0,79 "

TECHNICAL DATA

Characteristics

- Weight: 0,033 Kg / 0,07 Lb
- Housing in plastic UL 94 V-0
- Impeller in plastic UL 94 V-0
- L-10 life expectancy at 40°C: 70.000 hours
- Operating temperature range: -10 / +70 °C
- Storage temperature: -40 / +75°C
- Connection: Leads
- Brushless DC motor
- Integrated circuit
- IP20



Options

- Speed sensor
- Alarm
- Other IP levels

ELECTRICAL AND AERAULIC DATA

Part Number	Voltage	Voltage range	Airflow		Pressure		Nominal speed	Noise level LP	Nominal current	power
	V		l/s	CFM	mm H ² o	inch H ² o	RPM	dBA	mA	W
380DL5LP11000	5	4,5-5,5V	2,61	5,53	3,45	0,14	5000	22	100	0,50
380DL1LP11000	12	7-13,8V	2,61	5,53	3,45	0,14	5000	22	50	0,60
380DL2LP11000	24	14-27,6V	2,61	5,53	3,45	0,14	5000	22	40	0,96
380DM5LP11000	5	4,5-5,5V	3,38	7,17	5,54	0,22	6300	24	150	0,75
380DM1LP11000	12	7-13,8V	3,38	7,17	5,54	0,22	6300	24	60	0,72
380DM2LP11000	24	14-27,6V	3,38	7,17	5,54	0,22	6300	24	50	1,20
380DH5LP11000	5	4,5-5,5V	4,03	8,54	7,69	0,30	7600	29	250	1,25
380DH1LP11000	12	7-13,8V	4,03	8,54	7,69	0,30	7600	29	80	0,96
380DH2LP11000	24	14-27,6V	4,04	8,56	7,68	0,30	7600	29	60	1,44
380DS5LP11000	5	4,5-5,5V	4,45	9,43	9,00	0,35	8200	31	300	1,50
380DS1LP11000	12	7-13,8V	4,45	9,43	9,00	0,35	8200	31	100	1,20
380DS2LP11000	24	14-27,6V	4,45	9,43	9,00	0,35	8200	31	70	1,68
380DX5LP11000	5	4,5-5,5V	4,77	10,11	10,57	0,42	9000	33	320	1,60
380DX1LP11000	12	7-13,8V	4,77	10,11	10,57	0,42	9000	33	120	1,44
380DX2LP11000	24	14-27,6V	4,77	10,11	10,57	0,42	9000	33	90	2,16

DRAWING AND AIRFLOW CURVE



Non contractual document. All specifications are subject to change without prior notice. For professional use only. Please refer to the conditions of use of our catalogue.