

Circuit Breakers

R185 Series



Features

- Type III Manual Reset with Push-to-Trip Switch
- IP67 Water Resistant, Splash and Dust Proof Housing
- Single Pole, Thermal Device
- Ignition Protected
- Meets SAE J1171 External Ignition Protection of Marine Electrical Devices
- 1/4-28 Threaded Studs
- Surface Mount, Protective Stud Insulator Included
- Typically Used in DC Power Systems in Marine, Truck, and RV Applications. Add On Protection for Accessories



Thermal Circuit Breaker, Hydraulic and Hi-Amp Protector

D96



Electrical Specifications

Electrical Characteristics

Rating: 25A to 150A

Interrupt Rating: 3000 Amps @ 48 VDC; 2500 Amps @ 14 VDC

Insulation Resistance: 100 megohms @ 500 VDC

Dielectric Strength: 1800V, 1 minute

Mechanical Characteristics

Termination: 1/4-28 threaded stud

Mounting: Surface Mount

Environmental Characteristics

Operating: -32°C to +82°C

Storage: -34°C to +149°C

Trip Times

Rated Load	Trip Times
100%	Hold, No Trip within 30 Minutes
135%	Trip within 30 Minutes
200%	Trip within 60 Seconds