
molex



Part Number : 878342411
Product Description : 2.54mm Pitch C-Grid Header, Dual Row, Low Profile, Vertical, Shrouded, Lead-Free, 24 Circuits, Gold (Au) Flash, Beige, PCB Locators, without End Window
Series Number : 87834
Status : Active
Product Category : PCB Headers and Receptacles

Documents and Resources

Drawings

878342411_sd.pdf

PK-87835-001-001.pdf

3D Models and Design Files

STEP AP242

Creo

Symbol and Footprint (Multi-Format)

Specifications

713080001-AS-000.pdf

PS-70246-100-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	87834
Description	2.54mm Pitch C-Grid Header, Dual Row, Low Profile, Vertical, Shrouded, Lead-Free, 24 Circuits, Gold (Au) Flash, Beige, PCB Locators, without End Window
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	C-Grid
UPC	822348271597

Agency

UL	E29179

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V DC

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Natural
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	3.517/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PC Tail Length	3.43mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.127µm
Plating min - Termination	1.905µm
Polarized to Mating Part	Center Slot
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-55° to +120°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1

Downloaded from Arrow.com.

Max-Temp	265

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	1.27mm Pitch Ribbon Cable Connectors

Downloaded from Arrow.com.