




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL FOR EAR# RJ19077	JUN11/19	L.CHAN



FRONT VIEW



SIDE VIEW



BACK VIEW



MATERIALS:

HOUSING: ENGINEERING THERMOPLASTIC.
FLAMMABILITY RATING UL 94V-0

CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES. SEE PART NO. FOR THICKNESS.
50μ [1.27 MICRONS] MIN. NICKEL UNDERPLATE.
100μ [2.54 MICRONS] MIN. MATTE TIN OR GOLD FLASH ON CONTACT TAILS.

SHIELD: COPPER ALLOY
PLATING: NICKEL WITH TIN DIPPED PCB TAIL.


UNLESS OTHERWISE SPECIFIED, THE TOLERANCE IS ±0.015[±0.38]

PART NUMBER: RJSAE-XF80-A8

GOLD PLATING OPTION:

- D=6u" GOLD PLATING
- G=15u" GOLD PLATING
- J=30u" GOLD PLATING
- 5=50u" GOLD PLATING

CONNECTOR OUTLINE




P.C.B. HOLE LAYOUT
(COMPONENT SIDE OF BOARD)

LOCATE HOLES

⌀.005[0.13]

HOLES DIMENSIONS ARE BASIC



RECOMMENDED PANEL LAYOUT

UNLESS SPECIFIED OTHERWISE		DRAWN RONNIE.C	JUN11/19	Amphenol Canada Corp.	
PRIMARY UNITS INCHES	CHECKED L.CHAN	JUN11/19		Commercial Products	
SECONDARY MILLIMETERS	M.E. APP'D			TITLE STACKABLE MULTI-PORT MODULAR JACK, 8 POS. 8 CONTACTS, SHIELDED WITHOUT TAB, WITH .130INCH CONTACT TAILS, -RoHS COMPLIANT	
REFERENCE IN PARENTHESES	Q.A. APP'D			DWG NO. P-RJSAE-XF80-A8	
1 DECIMAL PLACE	DWG APP'D			REV A	
2 DECIMAL PLACES	ENG. REL. NO.			CODE ID NO. 03554 DWG SIZE SCALE SHEET 1 OF 1	
3 DECIMAL PLACES ±0.015	REF. EAR# RJ19077				
ANGULAR DEGREES ±1.5°	THIRD ANGLE PROJECTION				