



E32-T14 2M

Fiber optic sensor head, through-beam, long distance detection, square, side-view, R25 fiber, 2 m cable

Specifications

Sensing method	Through-beam
Shape	Square
Product Width (unpacked)	10.5 mm
Product Depth (unpacked)	8 mm
Product Height (unpacked)	25.2 mm
Application	Long distance detection
Features	Built-in lens
Temperature range	-40-70 °C
Sensing distance	4000 mm
Cable length	2 m
Bending radius	25 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Side-view
Material sheath	Polyethylene

Related products



E3X-ZV and E3X-MZV
Smart Fiber Amplifier



E3NX-CA
High-performance color
mark sensor



E3NX-CA
High-performance color
mark sensor



E3NX-MA
Smart Fiber Amplifier Units



E3X-NA
Digital fiber amplifier with
potentiometer adjustment



E3NX-FA
High-performance digital
fiber amplifier

Downloads

CAD Library



**E32-LT/LD Hex-shaped
Fiber Unit**
Brochure

EN PDF 6.35 MB



**Fiber Sensor Selection
Selection Guide**

EN PDF 15.9 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 3 May, 2026. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU