



Part Number : 1202530030
Product Description : Contrinex Inductive Sensor, M8 Housing, 6mm Operating Distance, Non-embeddable, PNP, NO, 3-pin M8 Connector, 60mm Housing Length
Series Number : 120253
Status : Active
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AS-513-M8-001




Documents & Resources

Specifications
1202530024-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Inductive and Photoelectric Sensors
Series	120253
Description	Contrinex Inductive Sensor, M8 Housing, 6mm Operating Distance, Non-embeddable, PNP, NO, 3-pin M8 Connector, 60mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130062003

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 500 Hz

Physical

Connection	Connector (M8, 3-pin)
Length	60mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP (PPS)
Mounting Style	Non-embeddable
Operating Distance	6mm
Output	NO
Sensor Housing Size	M8
Temperature Range - Operating	-25° to +70°C