


Technical drawing of a mechanical part showing dimensions and tolerances. The drawing includes the following dimensions and tolerances:

- Overall length: Dim L
- Overall width: 29.0
- Bottom flange thickness: 5.0
- Distance from left edge to first hole center: 3.81
- Distance between hole centers: 7.62
- Overall width of the bottom flange: Dim B

The drawing also shows a cross-section of the part, indicating a central hole and a flange. A wavy line indicates a break in the part.



DIM		TOL			
		2P-5P	6P-10P	11P-13P	14P-16P
Dim L	N×7.62	±0.20	±0.30	±0.35	±0.40
Dim B	(N-1)×7.62	±0.20	±0.30	±0.35	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	04/08/09	The current rating and operating temperature are changed	Jacke
△	04/08/09	Added cULus standard	Jacke
△	2010.01.30	The material is changed from Brass to Copper	Jacke
△	07/31`12	Added TUV standard	Chen Bo
△	07/31`12	The IEC spec is removed	Chen Bo
△	07/31`12	Soldering temperature changed from 250°C±10°C/5Sec to 260°C± 5°C/5Sec	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

3 ● Item a Male contact pin : Copper with Tin plated
● Item b Terminal (housing):Thermoplastic (UL94V-0)

5	Electrical	cULus	TUV
●	Voltage rating:	300V	800V
1	● Current rating:	32A	32A
●	Withstanding Voltage:	1.6KV	6KV
6	● Operating temperature:	-40°C to +115°C	
2	● Soldering temperature:	260°C ± 5°C/5 Sec	
4	● Safety Approval:	cULus	TUV
●	Critical dimension:	▽	

VC xx 00 x 1 xxxx G

Solid Block
02 2 POLES
03 3 POLES

- G RoHS compliant (lead<4%)
In copper Alloy

000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

COLOR

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VC 7.62 SERIES Vertical (180D)			
PART NO.		VCxx00x1xxxxG		DWG NO.	8VC0002
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Chen Bo 07/31'12	Chen Bo 07/31'12		UNIT: mm
					SCALE: NONE
				SHEET: 01/01	REV: E
					X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°