

Johanson Part Number EMCF160W103M1GV001T

Johanson Part Number: EMCF160W103M1GV001T	Johanson Company: JDI
Legacy P/N: 160X07W103MV4T	Size for Capacitors (EIA): 0402
Description: EMI Filters, 0402, X7R, 16.0V, 0.010 μ F $\pm$ 20%, Ni/Sn (RoHS), 7" Reel Paper Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.020
Schedule B: 8532.24.00.20	Thickness (Min): None
ITAR: No	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.011
RoHS Compliance: Yes, RoHS 10/10	Standard Item: Yes
REACH: Yes	Lead Time Typical (Weeks)*: 30
Country of Origin: US, MX, or CN	Length (Min): 0.042
Product Family: Capacitors	Length (Max): 0.048
Product Subfamily: EMI Filters	Width (Min):0.022
Capacitance Value: 0.010	Width (Max): 0.028
Cap Unit of Meas: μ F	Part Weight (mg): 2.20
Tolerance: $\pm$ 20%	Packaged Width (lb) Arm: None
Voltage: 16.0	Packaging: 7" Reel Paper Tape
Dielectric Temp Coefficient: X7R	Packaging Qty: 4000
Termination: 68	Operating Temp Range: -55°C to +125°C
Marking: No Mark	Storage Temp Range (Packaged): +5°C to +40°C with RH 20% to 70%
Product Release Date: Jan. 9, 2006	Storage Temp Range (None Operating): -65°C to +125°C
Harmonization: 8532.24.00.20	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansondielectrics.com/emi-filter-decoupling-capacitors>

Printed from: <https://www.johansontechnology.com/part/EMCF160W103M1GV001T/>