

Features

- Standard Vz Tolerance is $\pm 2\%$
- Planar Die Construction
- Ideally Suited for Automated Assembly Processes




Mechanical Data

- Package: SOD-323 package name
- Moisture Sensitivity: Level 1, per J-STD-020
- Halogen Free. "Green" Device (Note1)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish & RoHS Compliant
- Weight: 0.004 g (approximate)



SOD-323

Body Marking and Pin Layout

Body Marking	Internal structure
 XX: Device Marking Code¹ Bar: Cathode Pin Dot (optional): Manufacturing site marking ¹ Refer to the Marking Code for the specific device code.	 1 Cathode 2 Anode

Ordering Information

Product Name	Reel Size	Packing Type	Qty/Reel
BZT52B3V0JS-TP THRU BZT52B75JS-TP	7"	Tape & Reel	3,000
BZT52B3V0JS -13P THRU BZT52B75JS -13P	13"	Tape & Reel	10,000

For packaging details, visit our website at <https://www.mccsemi.com/Package/List>

Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Rating	Unit
Power Dissipation ^(Note2)	P_D	200	mW
Maximum Instantaneous Forward Voltage @ $I_F = 10\text{mA}$	V_F	0.9	V
Operating Junction Temperature Range	T_J	-55 to 150	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	-55 to 150	$^{\circ}\text{C}$

Thermal characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Rating	Unit
Thermal Resistance from Junction to Ambient ^(Note 2)	$R_{\theta JA}$	625	$^{\circ}\text{C/W}$

Notes:

1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. Mounted on PCB.






Electrical Characteristics (T_A=25°C unless otherwise specified)

Part Number	Zener Voltage ^(Note 3)			Test Current		Maximum Dynamic Impedance		Maximum Reverse Leakage Current		Typical Temperature Coefficient		Marking Code
	V _Z @I _{ZT}			I _{ZT}	I _{ZK}	Z _{ZT} @I _{ZT}	Z _{ZK} @I _{ZK}	I _R	V _R	S _Z @I _{ZT}		
	Min(V)	Typ(V)	Max(V)	mA	mA	Ω	Ω	μA	V	Min (mV/°C)	Max (mV/°C)	
BZT52B3V0JS	2.94	3	3.06	5	1	89	564	9	1	-3.5	0	2Z
BZT52B3V3JS	3.23	3.3	3.37	5	1	89	564	4.5	1	-3.5	0	3Z
BZT52B3V6JS	3.53	3.6	3.67	5	1	84	564	4.5	1	-3.5	0	4Z
BZT52B3V9JS	3.82	3.9	3.98	5	1	84	564	2.7	1	-3.5	0	5Z
BZT52B4V3JS	4.21	4.3	4.39	5	1	84	564	2.7	1	-3.5	0	6Z
BZT52B4V7JS	4.61	4.7	4.79	5	1	75	564	2.7	2	-3.5	0.2	7Z
BZT52B5V1JS	5.00	5.1	5.2	5	1	60	480	2	2	-2.7	1.2	2W8
BZT52B5V6JS	5.49	5.6	5.71	5	1	40	400	1	2	-2	2.5	2W9
BZT52B6V2JS	6.08	6.2	6.32	5	1	10	150	3	4	0.4	3.7	2WA
BZT52B6V8JS	6.66	6.8	6.94	5	1	15	141	2	4	1.2	4.5	2WB
BZT52B7V5JS	7.35	7.5	7.65	5	1	15	80	1	5	2.5	5.3	2WC
BZT52B8V2JS	8.04	8.2	8.36	5	1	15	80	0.7	5	3.2	6.2	2WD
BZT52B9V1JS	8.92	9.1	9.28	5	1	15	100	0.5	6	3.8	7	2WE
BZT52B10JS	9.80	10	10.2	5	1	20	150	0.2	7	4.5	8	2WF
BZT52B11JS	10.78	11	11.22	5	1	20	150	0.1	8	5.4	9	2WG
BZT52B12JS	11.76	12	12.24	5	1	25	150	0.1	8	6	10	2WH
BZT52B13JS	12.74	13	13.26	5	1	30	170	0.1	8	7	11	2WI
BZT52B15JS	14.70	15	15.3	5	1	30	200	0.1	10.5	9.2	13	2WJ
BZT52B16JS	15.68	16	16.32	5	1	40	200	0.1	11.2	10.4	14	2WK
BZT52B18JS	17.64	18	18.36	5	1	45	225	0.1	12.6	12.4	16	2WL
BZT52B20JS	19.60	20	20.4	5	1	55	225	0.1	14	14.4	18	2WM
BZT52B22JS	21.56	22	22.44	5	1	51	235	0.045	15.4	16.4	20	PZ
BZT52B24JS	23.52	24	24.48	5	1	65	235	0.045	16.8	18.4	22	RZ
BZT52B27JS	26.46	27	27.54	5	0.5	75	282	0.045	18.9	21.4	25.3	SZ
BZT52B30JS	29.40	30	30.6	5	0.5	75	282	0.045	21	24.4	29.4	TZ
BZT52B33JS	32.34	33	33.66	5	0.5	75	306	0.045	23	27.4	33.4	UZ
BZT52B36JS	35.28	36	36.72	5	0.5	84	329	0.045	25.2	30.4	37.4	VZ
BZT52B39JS	38.22	39	39.78	5	0.5	122	329	0.045	27.3	33.4	41.2	WZ
BZT52B43JS	42.14	43	43.86	5	0.5	141	353	0.045	30.1	37.6	46.6	XZ
BZT52B47JS	46.06	47	47.94	5	0.5	160	353	0.045	33	42	51.8	YZ
BZT52B51JS	49.98	51	52.02	5	0.5	169	376	0.045	35.7	46.6	57.2	ZZ
BZT52B56JS	54.88	56	57.12	2.5	1	135	1000	0.1	42	52.2	63.8	X2
BZT52B62JS	60.76	62	63.24	2.5	1	150	1000	0.1	46	58.8	71.6	X3
BZT52B68JS	66.64	68	69.36	2.5	1	200	1000	0.1	51	65.6	79.8	X4
BZT52B75JS	73.5	75	76.5	2.5	1	250	1000	0.1	56	73.4	88.6	X5


Notes:

3. Short-duration test pulses are used to minimize the self-heating effect.

Curve Characteristics



Package Outline




DIM	INCH		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.031	0.045	0.80	1.15*	Note 1
A1	0.000	0.006	0.00	0.15	
b	0.010	0.016	0.25	0.40	
c	0.003	0.010	0.08	0.25	
D	0.090	0.107	2.30	2.70	
D1	0.063	0.071	1.60	1.80	
E	0.045	0.055	1.15	1.40	
L1	0.004	0.018	0.10	0.45	

Notes:

1. Dimension A for products from manufacturing site VN is controlled at max 1.10 mm.

Suggested Pad Layout (Unit:mm)



Notes:

1. The suggested land pattern dimensions have been provided for reference only.
2. For further information, please refer to document IPC-7351A.

DISCLAIMERS

Micro Commercial Components Corp. (MCC) reserves the right to make changes to any product without prior notice, including corrections, modifications, enhancements, improvements, or other changes. MCC's products are not designed, authorized, or warranted for use in medical, military, aircraft, space, or life support equipment, nor in applications where failure or malfunction of an MCC product can reasonably be expected to result in personal injury, death, or severe property or environmental damage. MCC does not assume liability for any application or use of the products described herein, nor does it convey any license under its patent rights or those of others. Users of MCC's products in any such application assume all risks associated with their use and agree to hold MCC and all companies whose products are represented on our website harmless against any damages. MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of MCC.

Counterfeiting of semiconductor parts is an increasing problem in the industry. MCC is taking strong measures to protect both ourselves and our customers from counterfeit products. We strongly encourage customers to purchase our parts either directly from MCC or through Authorized Distributors, who are listed by country on our website. Products purchased directly from MCC or from Authorized Distributors are genuine, have full traceability, and meet our quality standards for handling and storage. MCC will not provide warranty coverage or any other assistance for parts bought from Unauthorized Sources.

This document, along with the item(s) described within, may be subject to export control regulations. Exporting these items may require prior authorization from national authorities.

Terms and Conditions - MCC products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.