

Han 22HPR-HTE-S-4xM20



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 40 022 0470 |
| Specification | Han 22HPR-HTE-S-4xM20 |
| HARTING eCatalogue | https://b2b.harting.com/19400220470 |

Identification

| | |
|--------------------------|---------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] HPR slim |
| Type of hood/housing | Hood |

Version

| | |
|----------------------|---------------------------------------|
| Size | 22 HPR |
| Version | Top entry |
| Cable entry | 4x M20 |
| Locking type | Screw locking |
| Field of application | Hoods/housings for harsh environments |

Technical characteristics

| | |
|--|--|
| Tightening torque (screw locking) | 4 Nm |
| Tightening torque | 10 Nm Fixing screws 15 Nm PE screw |
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP66 IP68 IP69 / IPX9K acc. to ISO 20653 |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |



Pushing Performance

Material properties

| | |
|--------------------------------------|---|
| Material (locking) | Stainless steel |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel |
| | Lead |
| | Naphthalene |

Specifications and approvals

| | |
|----------------|------------|
| Specifications | IEC 61984 |
| | EN 60664-1 |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 933 g |
| Country of origin | China |
| European customs tariff number | 85389099 |
| eCl@ss | 27440202 Shell for industrial connectors |