



Part Number : [1300060426](#)


Product Description : Mini-Change A-Size Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 16 AWG, Yellow PVC Cable, 1.83m (6.0') Length

Series Number : 130006

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 103001A01F060




Documents and Resources

Drawings

[1300060426 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 16 AWG, Yellow PVC Cable, 1.83m (6.0') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	78172553641

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Physical

Cable Diameter	10.41mm (.410")
Cable Length	1.83m (6.0')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail

Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	72.121/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	STOOW
Wire Size (AWG)	16

This document was generated on Apr 23, 2026