




44A0211-20-90-MX Product Details

 Share  Print  Email



 Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

44A0211-20-90

44A0211-20-90-MX 

TE Internal Number: 287045-000

Product Highlights [View All](#)

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 20 AWG
- Voltage Rating = 1000 VAC

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through Distributor 

Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Cable Type  Spec 44

Cable Style  Primary

Electrical Characteristics

Voltage Rating (VAC) 1000

Dimensions

Conductor Outer Diameter (mm [in]) 1.01 [0.040]

Body Features

Wire Size (AWG/CM) 20 AWG

Conductor Type Tin-Coated Copper

Wire Color White w/ Black Stripe

Nominal Outside Diameter (mm [in]) 1.57 [0.062]

Wire Diameter (mm [in]) 1.57 [0.062]

Configuration Features

Number of Conductors 1

Industry Standards

Government/Industry Qualification No

RoHS/ELV Compliance  RoHS compliant, ELV compliant

Lead Free Solder Processes  Not relevant for lead free process

RoHS/ELV Compliance History Always was RoHS compliant

Conditions for Usage

Temperature Range (°C) -65 – +150

Wire Size - Details 20 AWG 0.62 mm², 0.00095 in², 19 x 32 AWG

Operation/Application

Application General Purpose

Packaging Features

Wire Source United States

Other

Brand Raychem

Node Classification Hook Up Wire

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE

Investors

News Room

Supplier Portal

Careers

Terms & Conditions

Privacy Policy

Global Accessibility Statement

Quick Links

Distributor Inventory

Product Cross Reference

Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us

Find a Phone Number

Knowledge Base

Manage Your Account

Keep Me Informed

