




	1	2	3	4	5	6	7																																																																																									
A	 Material & finish SHELL: Steel Zinc plated PIN CONTACT: Brass Gold flash selective gold plated INSULATOR: PBT & Glass-fibre reinforced UL 94V-0 Blue NUMBER OF CONTACT: 14,24,36,50 CURRENT RATING: 5 Amp DIELECTRIC STRENGTH: 1000V for one minute INSULATOR RESISTANCE: 1000M Min. (at 500V DC) TEMPERATURE: -55°C to +105°C							A																																																																																								
B								B																																																																																								
C								C																																																																																								
D								D																																																																																								
E	 Dimensions <table><tr><th>Positions</th><th>A</th><th>B</th><th>C</th><th>D</th></tr><tr><td>14</td><td>12.96</td><td>25.2</td><td>36.0</td><td>44.1</td></tr><tr><td>24</td><td>23.76</td><td>36.0</td><td>46.8</td><td>54.9</td></tr><tr><td>36</td><td>36.72</td><td>48.9</td><td>59.7</td><td>67.9</td></tr><tr><td>50</td><td>51.84</td><td>64.1</td><td>74.9</td><td>83.0</td></tr></table>							Positions	A	B	C	D	14	12.96	25.2	36.0	44.1	24	23.76	36.0	46.8	54.9	36	36.72	48.9	59.7	67.9	50	51.84	64.1	74.9	83.0	E																																																															
Positions	A	B	C	D																																																																																												
14	12.96	25.2	36.0	44.1																																																																																												
24	23.76	36.0	46.8	54.9																																																																																												
36	36.72	48.9	59.7	67.9																																																																																												
50	51.84	64.1	74.9	83.0																																																																																												
F	CENTRONIC SOLDER FEMALE TYPE WITH SPRING LATCH							F																																																																																								
G	RoHS compliant <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>30.06.2009</td><td>Dean</td><td></td></tr><tr><td>X.</td><td>±0.38</td><td></td><td></td><td></td><td></td><td>Approved</td><td>30.06.2009</td><td>Hellwig</td><td></td></tr><tr><td>X.X</td><td>±0.25</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.13</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X°</td><td>±3°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>.X°</td><td>±1.0°</td><td>①</td><td>Drawn</td><td>30.06.2009</td><td>Dean</td><td colspan="2" rowspan="2"></td><td>ASS 0680 CO</td><td>rev01</td></tr><tr><td></td><td></td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td>Replace</td><td>Sheet</td></tr></table>							Scale	1:1						Date	Name	Customer-No.	TOLERANCE						Drawn	30.06.2009	Dean		X.	±0.38					Approved	30.06.2009	Hellwig		X.X	±0.25									X.XX	±0.13									Angle	TOL									X°	±3°									.X°	±1.0°	①	Drawn	30.06.2009	Dean			ASS 0680 CO	rev01			Id.	Modification	Date	Name	Replace	Sheet	G
Scale								1:1						Date	Name	Customer-No.																																																																																
TOLERANCE						Drawn	30.06.2009	Dean																																																																																								
X.	±0.38					Approved	30.06.2009	Hellwig																																																																																								
X.X	±0.25																																																																																															
X.XX	±0.13																																																																																															
Angle	TOL																																																																																															
X°	±3°																																																																																															
.X°	±1.0°	①	Drawn	30.06.2009	Dean			ASS 0680 CO	rev01																																																																																							
		Id.	Modification	Date	Name			Replace	Sheet																																																																																							
H								H																																																																																								
	1	2	3	4	5	6	7	SV/xxx																																																																																								