



Pushing Performance

# Han High Density module, crimp male




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 025 3001
Specification	Han High Density module, crimp male
HARTING eCatalogue	<a href="https://b2b.harting.com/09140253001">https://b2b.harting.com/09140253001</a>

## Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® High Density module

## Version

Termination method	Crimp termination
Gender	Male
Number of contacts	25
Details	Please order crimp contacts separately.

## Technical characteristics

Conductor cross-section	0.09 ... 0.52 mm²
Rated current	4 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance

## Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076

## Commercial data

Packaging size	2
Net weight	8.12 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)