



HONEYWELL PART NUMBER
12SM825
PRODUCT CODE TXA8295

REV	DOCUMENT	CHANGED BY	CHECK
6	0038111	PK 20MAY08	ASD



NOTE -
△-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
2-TERMINALS ARE PLATED FOR SOLDERING
3-SWITCH WILL WITHSTAND TEMPERATURE OF 300°F
4-CONTACT MATERIAL-24 K GOLD PLATED

RELEASE NO.	PR - 2786
REPLACES	-

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 	DRAWN	VK	17OCT07	Honeywell			
OPERATING FORCE — — — 3 OZ MAX	CONTACT ARRANGEMENT SPDT				CHECK	RJ	17OCT07				
RELEASE FORCE— — — — 1 OZ MIN	30 VOLTS DC RATING				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .002 MAX		SEA LEVEL	50,000 FT								
	INDUCTIVE	1/2 AMP	1/2 AMP								
OVERTRAVEL — — — — — .003 MIN	RESISTIVE	1 AMP	1 AMP	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE B	TYPE I	DRAWING NAME 12SM825	REV 6	
APPROVALS		MAXIMUM INRUSH 2 AMP					SHEET 1 OF 1				
	KEMA, CE	1A, 250V ~ T85 1E4									
	UL, CSA	1A, 125 VAC 30 VDC	  BRAND L184								
							WEIGHT .006LB MAX				