



STRAIGHT JACK FOR PRINTED CIRCUIT




PACKAGING BY 100

R141.426.168


Series : BNC



PANEL CUT OUT



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATINGS (µm)
BODY	BRASS	-
CENTER CONTACT	BRONZE	-
OUTER CONTACT	-	--
INSULATOR	PTFE	-
GASKET	-	-
OTHERS PARTS	-	--
-	-	-
-	-	-

Issue : 1122 C

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



STRAIGHT JACK FOR PRINTED CIRCUIT**R141.426.168****PACKAGING BY 100**Series : **BNC****PACKAGING**

Standard	Unit	Other
100	Option W	Contact us

SPECIFICATION**ELECTRICAL CHARACTERISTICS**

Impedance	50	Ω
Frequency	0-1.5	GHz
VSWR	1.08* + 0,0060	x F(GHz) Maxi
Insertion loss	.025*	$\sqrt{F}(\text{GHz})$ dB Maxi
RF leakage	- (NA	- F(GHz)) dB Maxi
Voltage rating	500	Veff Maxi
Dielectric withstanding voltage	1500	Veff mini
Insulation resistance	5000	M Ω mini

ENVIRONMENTAL

Operating temperature	-35/+70	$^{\circ}\text{C}$
Hermetic seal	NA	Atm.cm3/s
Panel leakage	NA	

OTHERS CHARACTERISTICS

Assembly instruction

Others :

* Coaxial Transmission Line Only

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	15 N mini
Axial force – Opposite end	15 N mini
Torque	NA N.cm mini
Recommended torque	
Mating	NA N.cm
Panel nut	NA N.cm
Mating life	100 Cycles mini
Weight	1,4000 g

Issue : 1122 C

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

