


THIS DOCUMENT AND THE DATA DISCLOSED
HEREIN OR HERewith IS NOT TO BE REPRODUCED,
USED, OR DISCLOSED IN WHOLE OR IN PART
TO ANYONE WITHOUT PERMISSION OF VICOR CORP.

ORIG. MJW DBASE LOST-REDRAW
DIM & SPEC CHANGES

LTR.	DESCRIPTION	DATE	APP'D.
1	RELEASED PER ECO #2212 J.W	10/11/90	BJR
2	REVISED PER E910258 J.W	05/14/91	BJR
3	REVISED PER E064340 REJH	05/22/06	CR

ELECTRICAL CHARACTERISTICS

RATED VOLTAGE:	250 VAC, 50/60 Hz
CAPACITANCE:	1500 pf ± 20%
DISSIPATION FACTOR:	≤1.3 MEASURED AT 1 KHZ
MAXIMUM PULSE RISE TIME:	du/dt 2000V / μSEC
TEST VOLTAGE:	(ELECTRODE/ELECTRODE) 2700 VDC 1 SEC, +23°C
INSULATION RESISTANCE:	120000 MΩ 500 VDC 1 MIN.



NOTES:

- 1. MATERIAL: METALLIZED PAPER, PLASTIC CAN, EPOXY RESIN SEALED IN SELF-EXTINGUISHING MATERIAL MEETING THE REQUIREMENTS OF UL 95V-0
- 2. TEMP RANGE: -40 TO +100 DEG C
- 3. APPROVALS INCLUDE: S, N, D, FI, VDE, SEV, IMQ, UL, CSA
- 4. FOR ADDITIONAL DIMENSIONS AND TOLERANCES CONTACT VENDOR AND CHECK DATA SHEET
- 5. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION

		VICOR ANDOVER, MA. U.S.A.	
DRAWN: J. WITEK	9/90	AC-PAPER-CAPACITOR 1500pF, 250 VAC, (Y)	
CHECKED: M L S	9/90		
APPD: M L S	9/90		
ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) DO NOT SCALE DRAWING	TOLERANCES (EXCEPT AS NOTED) .XX ±.01 .XXX ±.005 FRACT ±1/64 ANGLES ± 1°0	DRAWING NO.	REV.
		00770	3
NEXT ASSY:	SCALE: 2X	SHEET 1 OF 1	