


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/18/12	
A		REVISED SHAPE	10/24/12	



X	PLATING
0	15 µin Gold
1	30 µin Gold
2	50 µin Gold

RECOMMENDED PCB LAYOUT
 (COMPONENT SIDE)

ADAM TECH

909 Ratway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MODULAR JACK GANGED, 2 PORT, 8P8C
 W/ LED1 & LED2 GREEN/YELLOW

DRAWN	AY	7/18/12	SIZE	PART NO.	REV.
CHECKED	NP	7/18/12	X	MTJG-2-88X1-FSG-PG-L16	A
APPROVED			REF:	S0005C	

SPECIFICATIONS:
 Material: PA66, glass filled, rated UL 94V-0
 Insulator color: Black
 Contacts: Phosphor Bronze
 Shield: Brass, Nickel plated
 Contact Plating: Gold Flash over Nickel underplate on contact area, Tin over Copper underplate on tails
 (See chart for thickness).
 Electrical:
 Voltage plating: 125 VAC RMS.
 Current plating: 1.5 Amp.
 Contact resistance: 20 Milliohms max.
 Insulation Resistance: 1000M ohm Min@ 500 VDC
 Dielectric Withstanding Voltage: 1000 VAC for 1 minute.
 Temperature Rating: Operating temperature: -40°C to +85°C
 Environmental: Lead free, RoHS compliant.

