



DIMENSIONS:

A	3.125" ±0.063
B	4.186" ±0.125
C	3.795" ±0.063
D	2.500" ±0.063
E	2.938" ±0.063
G	0.203" x 0.400" ±0.015



NOTE: ALL LEADS 8" OUT MIN.



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 120V, 60Hz, WHT - BLK	208mA	Max.
Sec. N.L.V	@ 120V, 60Hz, WHT - BLK		
	RED - RED =	520.6V	±2%
	RED - RED/YEL = RED/YEL - RED =	260.3V	±2%
	RED/YEL - VIO =	52.44V	±2%
	YEL - YEL =	5.197V	±2%
	YEL - YEL/BLK = YEL/BLK - YEL =	2.598V	±2%
	GRN - GRN =	6.614V	±2%
	GRN - GRN/YEL = GRN/YEL - GRN =	3.307V	±2%
DCR	@ 20°C, WHT - BLK =	3.124 Ω	±20%
	@ 20°C, BRN - BLU =	3.382 Ω	±20%
	@ 20°C, RED - RED =	64.46 Ω	±20%
	@ 20°C, YEL - YEL =	0.034 Ω	±20%
	@ 20°C, GRN - GRN =	0.022 Ω	±20%
HIPOT	PRIMARY - SECONDARY	2500V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	01/19/10	52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181			
			FAX # (519) 886-9540			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: POWER TRANSFORMER	DWG. NO. 370JX
			DATE: 01/19/10	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		