

SPC5675KFAVMS2 :Part Detail

General Information	Package Information	Environmental and Compliance Information	Manufacturing Information	Ordering Information
Operating Characteristics				

General Information

Part Number	SPC5675KFAVMS2
Description	Freescale 32-bit MCU, Dual Power Arch, 2MB Flash, 180MHz, -40/+105degC, Automotive Qual, MAPBGA473
Product Line	G9V5675A
PTI	JBCI
Material Type	Tested Packaged Device
Life Cycle Description (code) (/webapp/sps/site/eialink.jsp)	PRODUCT RAPID GROWTH
Status	Active
SafeAssure Functional Safety (http://www.nxp.com/about/about-nxp/technology-leadership/safeassure-functional-safety-program:SAFETYPRGRM)	Quality Managed
Application/Qualification Tier (/webapp/sps/site/aqtlink.jsp?type=pop_up)	AUTO; >=10 YEARS APPLICATION LIFE

Package Information

Package Type and Termination Count	MAPBGA473
Package Description and Mechanical Drawing	MAP 473 19*19*1.6 P0.8
Device Weight(g)	1.62330
Package Length (nominal)(mm)	19.000
Package Width (nominal)(mm)	19.000
Package Thickness (nominal)(mm)	1.600
Tape & Reel	No

Environmental and Compliance Information

Pb-Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PBFREE_INFO&type=pop_up)	
RoHS Compliant (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_INFO&type=pop_up)	
Halogen Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=HALOGEN_FREE_INFO)	Yes
Material Composition Declaration (MCD) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_MCD&type=pop_up)	Download MCD Report  (/mcds/SPC5675KFAVMS2.pdf) Download MCD Report  (/mcds/SPC5675KFAVMS2.xls)
RoHS Certificate of Analysis (CoA) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_COA&type=pop_up)	Contact Us (https://nxpcommunity.force.com/community/communityContactSupport)
2nd Level Interconnect (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PLATING_INDICATOR_INFO)	e2
Moisture Sensitivity Level (MSL)	3
Floor Life	168 HOURS
Peak Package Body Temperature (PPT)(°C)	260

Maximum Time at Peak Temperature (s)	40
Number of Reflow Cycles	3
REACH SVHC	NXP REACH Statement (/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf)
UL94 (plastics flammability test)	V0;Burning stops within 10 seconds on a vertical specimen;no drips allowed

Manufacturing Information

Micron Size(μm)	.09
-----------------	-----

Ordering Information

Minimum Package Quantity (MPQ)	420
MPQ Container	BRICK
Exempt from Minimum Delivery Value	Yes
Preferred Order Quantity (POQ)	840
POQ Container	BOX
Export Control Classification Number (US)	3A991A2
Harmonized Tariff (US) Disclaimer (/webapp/sps/site/harmTariffDisclaim.jsp)	8542.31.0000
CCATS Document	-
ENC Status	-
Other Trade Compliance Documents	-
Budgetary Price excluding tax(US\$) (/webapp/sps/site/bplink.jsp) Change Currency	-
Order	

Operating Characteristics

Sample Exception Availability	N
-------------------------------	---

ABOUT NXP

Investors (<http://investors.nxp.com/phoenix.zhtml?c=209114&p=irol-irhome>)
Partners (<http://www.nxp.com/webapp/connect/memberDirSearch.sp>)
Careers (<http://www.nxp.com/about/careers-at-nxp:CAREERS>)

RESOURCES

Mobile Apps (<http://www.nxp.com/about/nxp-mobile-applications:MOBILE>)
Press, News, Blogs (<http://media.nxp.com>)
Contact Us (<http://www.nxp.com/pages/contact-us:CONTACTUS>)

FOLLOW US

(<https://twitter.com/NXP>) (<http://www.linkedin.com/company/nxp-semiconductors>) (<https://www.facebook.com/NXPsemi>)

(<https://contact.nxp.com/Subscription-Center>)

News 16 Feb 2017

NXP Wins Prestigious Automotive Innovation Award with Radar
Read More (<http://phx.corporate-ir.net/phoenix.zhtml?c=254228&p=irol-newsArticle&cat=news&id=2246510>)

