




	1	2	3	4	5	6	7																																																																															
A						Material Terminal body (metal housing): Brass(CuZn) Terminal screw: Steel Zinc plating "-" slot type Contacts: Brass Surface of solder tail: Tin plated Insulator (housing): Thermoplastic (UL94V-0),Green Electrical cULus Voltage rating: 300VAC Current rating: 10A Wire range: Solid wire(AWG): 16-28 Stranded wire(AWG): 16-28 Torque(Lb-In): 1.7 Screw: M2 Wire strip length: 6-7mm Withstanding Voltage: 1.6KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval: 		A																																																																														
B								B																																																																														
C								C																																																																														
D								D																																																																														
E								E																																																																														
F								F																																																																														
	N=Number of contacts					P.C,B LAYOUT																																																																																
G	RoHS compliant  File No.: E349947					<table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>08.09.2009</td><td>Rale</td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td></td><td>Approved</td><td>08.09.2009</td><td>Hellwig</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>②</td><td>UL Update</td><td>23.03.2017</td><td>C.Bakula</td><td colspan="3" rowspan="2"></td></tr><tr><td>X.°</td><td>±1°</td><td>①</td><td>Drawn</td><td>08.09.2009</td><td>Rale</td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td></td><td>Replace</td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td></tr></table>		Scale	1:1					Date	Name	Customer-No.	TOLERANCE						Drawn	08.09.2009	Rale	X.	±0.50					Approved	08.09.2009	Hellwig	X.X	±0.30								X.XX	±0.10								DIM	TOL	②	UL Update	23.03.2017	C.Bakula				X.°	±1°	①	Drawn	08.09.2009	Rale	X.X°	±X°					Replace			Angle	TOL	Id.	Modification	Date	Name				G
Scale						1:1					Date	Name	Customer-No.																																																																									
TOLERANCE											Drawn	08.09.2009	Rale																																																																									
X.	±0.50					Approved	08.09.2009	Hellwig																																																																														
X.X	±0.30																																																																																					
X.XX	±0.10																																																																																					
DIM	TOL	②	UL Update	23.03.2017	C.Bakula																																																																																	
X.°	±1°	①	Drawn	08.09.2009	Rale																																																																																	
X.X°	±X°					Replace																																																																																
Angle	TOL	Id.	Modification	Date	Name																																																																																	
H						<table><tr><td colspan="2">ASSMANN WSW-No. A-TB350-TVxxSB</td></tr><tr><td>Drawing-No. ASS 3710 CO</td><td>rev02</td></tr><tr><td>Replace</td><td>Sheet</td></tr></table>		ASSMANN WSW-No. A-TB350-TVxxSB		Drawing-No. ASS 3710 CO	rev02	Replace	Sheet	H																																																																								
ASSMANN WSW-No. A-TB350-TVxxSB																																																																																						
Drawing-No. ASS 3710 CO						rev02																																																																																
Replace	Sheet																																																																																					
	1	2	3	4	5	6	7	SV1635-1																																																																														