


COAXIAL CONNECTOR, BNC, 75 Ohm, Straight cable jack (female)
21_BNC-75-4-4/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
BNC	jack	Interface compatible with IEC 61169-8
Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating
Electrical data		
Impedance	75 Ω	
Interface frequency	1 GHz	
Mechanical data		
Weight	0.0136 kg	
Mating cycles	500	
Cable entry centre contact	crimped	
Cable entry outer contact	crimped	
Environmental data		
Operation temperature	-65 °C ... 165°C	

COAXIAL CONNECTOR, BNC, 75 Ohm, Straight cable jack (female)
21_BNC-75-4-4/133_N

Ordering Information Table		
Item number	Item description	Packaging type
22540872	21_BNC-75-4-4/133_NE	Single
Suitable cables		
Cable group	X16 - 4 mm / 75 Ohm --- obsolete (integrated in U18)	
	U16 - 4 mm / 75 Ohm	
Suitable cables	RG_59_B/U	
	GX_04273	
Additional Information		
Only as assembly	No	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2914 / Date of publication: 25.11.2023 / uncontrolled copy