

## **Conformal Coated Chip Optimized for Audio Applications**




### **FEATURES**

- Compliant to the RoHS2 directive 2011/65/EU
- Rich sound in the bass register and clear sound, Materials are strictly selected to achieve high level sound. F95 series has no lead-frame, and no vibration factor
- Low ESR, Low ESL
- Line up miniature size and high capacitance, necessary to mobile design
- SMD conformal
- Small and high CV







Single-side electrodes (Both electrodes at bottom side only)

#### **APPLICATIONS**

- Mobile Audio Player
- Smartphone
- Mobile phone
- Wireless Microphone System

### **CASE DIMENSIONS:** millimeters (inches)

-	Code	<b>EIA Code</b>	<b>EIA Metric</b>	L	W	Н	Α	В	C	D*
	В	1411	3528-20	3.50±0.20	2.80±0.20	1.80±0.20	0.80±0.30	1.20±0.30	1.10±0.30	0.20
				(0.138±0.008)	(0.110±0.008)	(0.071±0.008)	(0.031±0.012)	(0.047±0.012)	(0.043±0.012)	(0.008)
	s	1306	3216-12	3.20±0.30	1.60±0.30	1.00±0.20	0.80±0.30	1.20±0.30	0.80±0.30	0.20
				(0.126±0.012)	(0.063±0.012)	(0.039±0.008)	(0.031±0.012)	(0.047±0.012)	(0.031±0.012)	(0.008)
	_	1411	3527-12	3.50±0.20	2.70±0.20	1.00±0.20	0.80±0.20	1.20±0.20	1.10±0.30	0.20
	•	1411	3321-12	(0.138±0.008)	(0.106±0.008)	(0.039±0.008)	(0.031±0.008)	(0.047±0.008)	(0.043±0.012)	(0.008)

<sup>\*</sup>D dimension only for reference

### **MARKING**

**S CASE** 

B, T CASE





μF	68	100	150	220	330	470	680
code	W7	A8	E8	J8	N8	S8	W8

#### **HOW TO ORDER**

F95 0G Type Rated Voltage 227

Capacitance Code

pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

M

**Tolerance**  $K = \pm 10\%$  $M = \pm 20\%$ 

S Case

above

**Packaging** Size See Tape & Reel Packaging Section See table

AM<sub>1</sub>

**AUDIO Series** Code

Q2 Single Face

Electrode

### **TECHNICAL SPECIFICATIONS**

-55 to +125°C				
+85°C				
±20%, ±10% at 120Hz				
Refer to next page				
Refer to next page				
Refer to next page				
Provided that:				
After 1 minute's application of rated voltage, leakage current at 85°C				
10 times or less than 20°C specified value.				
After 1 minute's application of rated voltage, leakage current at 125°C				
12.5 times or less than 20°C specified value.				
+15% Max. at +125°C				
+10% Max. at +85°C				
-10% Max. at -55°C				



## **Conformal Coated Chip Optimized for Audio Applications**

# CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capac	itance	Rated Voltage						
μF	Code	4V (0G)	6.3V (0J)	10V (1A)				
68	686	S	S	В				
100	107	S	S/T	В				
150	157	S						
220	227	S/T	В					
330	337	Т	В					
470	477	В						
680	687							

Released ratings

Please contact to your local AVX sales office when these series are being designed in your application.

### **RATINGS & PART NUMBER REFERENCE**

AVX	Case	Capacitance	Rated	DCL	DF	ESR	10	OkHz RMS Current (n	nA)	*1	
Part No.	Size	(μ <b>F</b> )	Voltage (V)	(μΑ)	@ 120Hz (%)	@ 100kHz (Ω)	25°C	85°C	125°C	∆C/C (%)	MSL
4 Volt											
F950G686#SAAM1Q2	S	68	4	2.7	10	0.8	274	246	110	*	3
F950G107#SAAM1Q2	S	100	4	4.0	14	0.8	274	246	110	*	3
F950G157#SAAM1Q2	S	150	4	6.0	22	0.8	274	246	110	±15	3
F950G227#SAAM1Q2	S	220	4	8.8	30	0.8	274	246	110	±15	3
F950G227#TAAM1Q2	Т	220	4	8.8	25	0.6	365	329	146	*	3
F950G337#TAAM1Q2	T	330	4	13.2	40	0.8	316	285	126	±20	3
F950G477#BAAM1Q2	В	470	4	18.8	40	0.4	461	415	184	±20	3
					6.3	Volt					
F950J686#SAAM1Q2	S	68	6.3	4.3	14	0.9	258	232	103	*	3
F950J107#SAAM1Q2	S	100	6.3	6.3	20	0.9	258	232	103	±15	3
F950J107#TAAM1Q2	Т	100	6.3	6.3	14	0.6	365	329	146	*	3
F950J227#BAAM1Q2	В	220	6.3	13.9	30	0.4	461	415	184	*	3
F950J337#BAAM1Q2	В	330	6.3	20.8	35	0.6	376	339	151	±20	3
10 Volt											
F951A686#BAAM1Q2	В	68	10	6.8	12	0.4	461	415	184	*	3
F951A107#BAAM1Q2	В	100	10	10.0	14	0.4	461	415	184	*	3

<sup>\*1: \( \</sup>Delta C/C \) Marked "\*"

Item	All Case (%)				
Damp Heat	±10				
Temperature cycles	±5				
Resistance soldering heat	±5				
Surge	±5				
Endurance	±10				

#: "M" for  $\pm 20\%$  tolerance, "K" for  $\pm 10\%$  tolerance.

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.



# **Conformal Coated Chip Optimized for Audio Applications**


### **QUALIFICATION TABLE**

TEST	AUDIO F95 series (Temperature range -55°C to +125°C)
IESI	Condition
Damp Heat (Steady State)	At 40°C, 90 to 95% R.H., 500 hours (No voltage applied) Capacitance Change
Temperature Cycles	At -55°C / +125°C, 30 minutes each, 5 cycles Capacitance Change
Resistance to Soldering Heat	10 seconds reflow at 260°C, 5 seconds immersion at 260°C. Capacitance Change
Surge	After application of surge voltage in series with a 33Ω resistor at the rate of 30 seconds ON, 30 seconds OFF, for 1000 successive test cycles at 85°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change
Endurance	After 2000 hours' application of rated voltage 85°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change
Shear Test	After applying the pressure load of 5N for 10±1 seconds horizontally to the center of capacitor side body which has no electrode and has been soldered beforehand on a substrate, there shall be found neither exfoliation nor its sign at the terminal electrode.
Terminal Strength	Keeping a capacitor surface-mounted on a substrate upside down and supporting the substrate at both of the opposite bottom points 45mm apart from the center of capacitor, the pressure strength is applied with a specified jig at the center of substrate so that the substrate may bend by 1mm as illustrated. Then, there shall be found no remarkable abnormality on the capacitor terminals.




## **Conformal Coated Chip Optimized for Audio Applications**

### **AVX SOLID ELECTROLYTIC CAPACITOR ROADMAP**



### **Five Capacitor Construction Styles**



### SERIES LINE UP: CONFORMAL Ta MnO<sub>2</sub>

