

10A, 100V - 200V Schottky Barrier Surface Mount Rectifier

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free


APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- DC to DC converters

MECHANICAL DATA

- Case: TO-263AB (D²PAK)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 1.40g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	10	A
V_{RRM}	100 - 200	V
I_{FSM}	120	A
$T_J \text{ MAX}$	175	°C
Package	TO-263AB (D ² PAK)	
Configuration	Dual dies	



TO-263AB (D²PAK)



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)					
PARAMETER	SYMBOL	MBRS 10H100CT	MBRS 10H150CT	MBRS 10H200CT	UNIT
Repetitive peak reverse voltage	V_{RRM}	100	150	200	V
Reverse voltage, total rms value	$V_{R(RMS)}$	70	105	140	V
Forward current	I_F	10			A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I_{FSM}	120			A
Peak repetitive forward current (Rated V_R , Square wave, 20KHz)	I_{FRM}	10			A
Peak repetitive reverse surge current ⁽¹⁾	I_{RRM}	1		0.5	A
Critical rate of rise of off-state voltage	dv/dt	10,000			V/ μs
Junction temperature	T_J	-55 to +175			°C
Storage temperature	T_{STG}	-55 to +175			°C

Notes:

1. $t_p = 2.0\mu\text{s}$, 1.0KHz

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-case thermal resistance	$R_{\theta JC}$	3.5	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	MBRS10H100CT MBRS10H150CT MBRS10H200CT	V_F	-	0.85	V
	$I_F = 5\text{A}, T_J = 25^\circ\text{C}$		-	0.88	V
	MBRS10H100CT MBRS10H150CT MBRS10H200CT		-	0.95	V
	$I_F = 10\text{A}, T_J = 25^\circ\text{C}$		-	0.97	V
	MBRS10H100CT MBRS10H150CT MBRS10H200CT		-	0.75	V
	$I_F = 5\text{A}, T_J = 125^\circ\text{C}$		-	0.85	V
Reverse current @ rated V_R per diode ⁽²⁾	MBRS10H100CT MBRS10H150CT MBRS10H200CT	I_R	-	5	μA
	$T_J = 125^\circ\text{C}$		-	1	mA

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE	PACKAGE	PACKING	DEVICE MARKING
MBRS10H100CT	TO-263AB (D ² PAK)	800 / Tape & Reel	MBRS10H100CT
MBRS10H150CT	TO-263AB (D ² PAK)	800 / Tape & Reel	MBRS10H150CT
MBRS10H200CT	TO-263AB (D ² PAK)	800 / Tape & Reel	MBRS10H200CT

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics






Fig.5 Maximum Non-Repetitive Forward Surge Current



CHARACTERISTICS CURVES


(T_A = 25°C unless otherwise noted)

Fig.6 Typical Transient Thermal Impedance



PACKAGE OUTLINE DIMENSIONS

TO-263AB (D2PAK)



MARKING DIAGRAM

P/N = Device marking
G = Green compound
YWW = Date code
F = Factory code

NOTES: UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS ARE IN MILLIMETERS.
- DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
- THE PACKAGE OUTLINE REFERENCE: JEDEC TO-263, VARIATION AB, ISSUE F.
- MOLDED PLASTIC BODY DIMENSIONS DO NOT INCLUDE MOLD FLASH. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREME OF THE PLASTIC BODY.
- DWG NO REF: HQ2SD07-TO263AB-008 REV A.

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.