






CONTACT DETAIL 5/1

- NOTE 1. CONTACT PLATING
CONTACT AREA: GOLD 0.2 μ m MIN.
TERMINATION AREA: GOLD 0.05 μ m MIN.
UNDERPLATING: NICKEL
2. THE MATERIAL OF SPACER

96	PA9T (GF)
20~68	PPS (GF)
Pos.	MATERIAL



PCR-E96FS+	96	69.9	61.61	1.27x (48-1) = 59.69	64.51	1, 48, 49, 96
PCR-E68FS+	68	52.1	43.83	1.27x (34-1) = 41.91	46.73	1, 34, 35, 68
PCR-E50FS+	50	40.7	32.4	1.27x (25-1) = 30.48	35.3	1, 25, 26, 50
PCR-E36FS+	36	31.8	23.51	1.27x (18-1) = 21.59	26.41	1, 18, 19, 36
PCR-E28FS+	28	26.7	18.43	1.27x (14-1) = 16.51	21.33	1, 14, 15, 28
PCR-E20FS+	20	21.65	13.35	1.27x (10-1) = 11.43	16.25	1, 10, 11, 20
PART No.	No. OF POS.	A	B	C	D	CONTACT POS. # MARKING
DIMENSION						

				4	SPACER	SEE NOTE#2	1	——	UL94V-0 BLACK			
③				3	SHELL	STEEL	1	NICKEL PLATING	——			
②				2	INSULATOR	PBT (GF)	1	——	UL94V-0 BLACK			
①				1	CONTACT	PHOSPHOR BRONZE	No. OF POS.	SEE NOTE#1	——			
LTR.	DATE	BY	REV.	DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE		
DATE		SCALE		UNIT		HONDA TSUSHIN KOGYO CO., LTD.						
May. 21. 2004		2 / 1		mm (INCH)							3RD. A. P	
APP. DATE&REV.												
DR.		DE.		CHK.		NAME		1.27mm SPACING (RoHS) SOLDER TYPE FEMALE CONNECTOR				
T. KAWANO		T. KAWANO		T. SOGO		K. HOMMA		K. SATO		REV		
PART NO.		PCR-E () FS+										