

171511-3 Product Details

SharePrintEmail



171511-3

TE Internal Number: 171511-3

Active

View 3D PDF

Ring and Spade Tongue Terminals

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = PLASTI-GRIP
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information	
Product Drawings: - RING TERMINAL PIDG (PDF, Japanese) Catalog Pages/Data Sheets: - None Available Product Specifications: - PLASTI-GRIP TERMINALS AND SPLICES WITH INSULATION SL... (PDF, English) Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version B) 3D Model (IGES, Version B) 3D Model (STEP, Version B)	Related Products: Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Terminal Shape = Ring Tongue - Receptacle Style = Straight - Barrel Type = Closed Barrel - Wire/Cable Type = Regular Wire - Insulation = Yes - Insulation Support = Non-Insulation Support - Stud Diameter (mm [in]) = 6.70 [0.264] - Stud Size = 1/4 [M6] - Shape = RING-041 - Heavy Duty = No - Finish = Tin - Color = Red Electrical Characteristics: - Voltage (VAC) = 600 Termination Features: - Wire/Cable Size (CMA) = 509 - 3,260 Dimensions: - Insulation Diameter (mm [in]) = 3.48 [.137] Max.	Body Features: - Body Style = PLASTI-GRIP - Wire Range (mm [AWG]) = 0.30-1.40² [22-16] - Material = Copper - Stock Thickness (mm [in]) = 0.79 [0.031] Industry Standards: - Government/Industry Qualification = No - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Not reviewed for lead free solder process - RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: - Temperature Range (°C) = 90 Packaging Features: - Packaging Method = Loose Piece Other: - Brand = AMP