




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **2.08 – 5.26 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	19.69 mm[.775 in]
Compatible Insulation Diameter Range	3.81 – 5.08 mm[.15 – .2 in]
Terminal Material Thickness	.46 mm[.018 in]
Wire Size	2.08 – 5.26 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	9000
Packaging Method	Strip/Reel

Other

Line	Budget
------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 KIT REPRESENTATION ONLY TE Part # 7-2150237-7 OCEAN_2.0_SPARE_PART_KIT-130F2100	 TE Part # 2150237-1 OCEAN_2.0_APPLICATOR-E-130F2100-REM	 TE Part # 314917-1 EXT TL 250 U-POD STR IS9726	 REPRESENTATION ONLY TE Part # 90120 DAHT 250 FASTON REC 14-10 ASSY
 TE Part # 58525-2 PROCRIMPER DIE	 TE Part # 2150237-2 OCEAN_2.0_APPLICATOR-E-130F2100-REA	 TE Part # 314916-1 INSERT TL 250 U-POD STR IS9725	 TE Part # 58525-1 PROCRIMPER TOOL & DIE
 TE Part # 735211-2 250 FASTON REC 14-10 AWG TPBR			

Also in the Series | **FASTON 250**



Compression Connectors(4)




Crimp Terminal Housings(115)



Insertion & Extraction Tools(6)



Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(133)



Quick Disconnects(417)




Splices(4)


Customers Also Bought




TE Part #52856-1
TERMINAL,PG SPD FLG 12-10 10



TE Part #60701-1
FF 250 TAB 14-10AWG TPBR



TE Part #63435-1
250 FASTON REC 14-10 AWG SPBR




TE Part #63537-2
250 FASTON REC 18-14 TPBR




TE Part #193797-1
SKT ASSY - 2MM, 10 AWG




TE Part #520974-2
ULTRA-POD 250 ASSY REC 14-12
AWG TPBR



TE Part #521053-1
250 FASTON HSG. REC 1P NATURAL



TE Part #5-530519-2
HIGH CURRENT CONT-STRIP



TE Part #794116-1
04P .156 MNL PLUG



TE Part #1742539-3
CLUSTER BLOCK RECEPT,TPCuFeP

Documents



Product Drawings

250 FASTON REC 14-10 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_63365-2_AF.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63365-2_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63365-2_AF.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Engineering Report

English

Agency Approvals

UL Report

English