




HONEYWELL PART NUMBER
4SX37-H58
PRODUCT CODE VDF0965

REV	DOCUMENT	CHANGED BY	CHECK
5	0038447	SS 28MAR08	BLR



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø.087 MAX ON .188 ± .002 CENTERS
 - 2 - PLATED TERMINALS WILL ACCEPT "AMP INC" Ø.058 PIN RECEPTACLES
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400° F
 - 4 - SEE SPECIFICATION OF MATING TERMINAL RECEPTACLE FOR TEMPERATURE LIMITATIONS
 - 5 - SWITCH HAS A GREATER OVERTRAVEL THAN STANDARD CONSTRUCTION. ADDITIONAL OVERTRAVEL WILL TEND TO REDUCE MECHANICAL LIFE

RELEASE NO.	PR-19988
REPLACES	X94396-SX

CHARACTERISTICS
OPERATING FORCE - - - - 5 OZ MAX
RELEASE FORCE - - - - - 1 OZ MIN
DIFFERENTIAL TRAVEL - - - .005 MAX
OVERTRAVEL - - - - - .010 MIN

ELECTRICAL DATA
CONTACT ARRANGEMENT SPDT
APPROVALS
KEMA, CE 7A 250V~ T125 5E4
UL, CSA 7A 250 VAC

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION

DRAWN	SPK	06FEB08
CHECK	RJ	06FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	4SX37-H58	5
SCALE	-	WEIGHT: .003 LB MAX	SHEET 1 OF 1