




RESISTANCE VS TEMPERATURE CHARACTERISTICS:

Temp(°C)	R min (KΩ)	R nom (KΩ)	R max (KΩ)	Temp(°C)	R min (KΩ)	R nom (KΩ)	R max (KΩ)
-40	291.2	304.4	318.1	50	3.49	3.561	3.634
-35	213.6	222.6	231.9	55	2.879	2.944	3.01
-30	158.3	164.4	170.8	60	2.388	2.446	2.505
-25	118.4	122.6	127	65	1.989	2.041	2.095
-20	89.39	92.32	95.34	70	1.664	1.711	1.759
-15	68.17	70.21	72.31	75	1.399	1.44	1.483
-10	52.38	53.81	55.27	80	1.18	1.217	1.256
-5	40.53	41.53	42.55	85	1.001	1.034	1.069
0	31.58	32.27	32.98	90	0.853	0.882	0.913
5	24.72	25.2	25.69	95	0.729	0.756	0.783
10	19.48	19.82	20.15	100	0.625	0.649	0.674
15	15.46	15.68	15.91	105	0.539	0.56	0.582
20	12.33	12.49	12.64	110	0.465	0.484	0.504
25	9.9	10	10.1	115	0.403	0.42	0.438
30	7.955	8.053	8.151	120	0.351	0.366	0.382
35	6.427	6.52	6.613	125	0.306	0.32	0.334
40	5.218	5.304	5.392	130	0.261	0.274	0.286
45	4.257	4.337	4.417	135	0.216	0.228	0.238

NOTES:

1. RESISTANCE @ 25°C : 10KΩ±2%
2. BETA VALUE (0/50°C) : 3892K±1%
3. OPERATING TEMPERATURE RANGE : -40°C TO +135°C.
4. DISSIPATION FACTOR : 1.5mW/°C
5. THERMAL TIME CONSTANT : LESS THAN 3SECONDS IN WATER
- 6.INSULATION RESISTANCE : 10MΩ AT 100 VDC

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
		mm		NTS													
		GENERAL TOLERANCES (UNLESS SPECIFIED)								EC NO: 657230 DRWN: RAVIKM CHK'D: RBBHASKAR APPR: RBBHASKAR				NTC EPOXY - 3892 25MM 10K2%			
		ANGULAR TOL ± °															
DIVISIONAL SYMBOLS		4 PLACES		±		2021/03/03				PRODUCT CUSTOMER DRAWING							
		3 PLACES		±		2021/03/05											
		2 PLACES		±		2021/03/05											
		1 PLACE		±		INITIAL REVISION: DRWN: RAVIKM APPR: RBBHASKAR				DOCUMENT NUMBER 2152725603		DOC TYPE PSD		DOC PART 000		REVISION A	
		0 PLACES		±													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
						A3-SIZE		215272		2152725603		OTS		1 OF 1			