

 **Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



## Quick Links

- 1.27 mm Centerline
- Nomex Insulation Material
- Insulation Length = 88.90 mm
- Pin Arrangement (Left) = D
- Pin Arrangement (Right) = D

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Part Number: 3-6437132-7

Active

 Add to Part List

## Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

**Product Specifications:**

- None Available

Application Specifications:

- None Available

**Instruction Sheets:**

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Additional Product Images:

- Product View
- Product View

Related Products:

- Tooling

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Insulation Material = Nomex
- Number of Conductors = 26

### Electrical Characteristics:

- Current Rating (Amps.) = 1.6
- Impedance ( $\Omega$ ) = 95
- Voltage Rating (VAC) = 200

Body Related Features:

- Centerline (mm [in]) = 1.27 [0.050]
- Insulation Length (mm [in]) = 88.90 [3.500]

Configuration Related Features:

- Pin Arrangement (Left) = D
- Pin Arrangement (Right) = D

### Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

### Conditions for Usage:

- Operating Temperature (°C [°F]) = -40 - +125  
[-40 - +257]

## Other:

- Brand = Tyco Electronics