






CONTACT DETAIL
(5/1)

NOTE1 . CONTACT PLATING

CONTACT AREA: Pd/Ni 0.5 μ m + GOLD 0.1 μ m MIN.

TERMINAL AREA: GOLD 0.05 μm

ALL OVER NICKEL UNDERPLATED

2. APPLICABLE CABLE COVER: P/N: HDRA-E () LGKP ()

3. MATING CONNECTOR: P/N: HDRA-E () LFDT-SL+

4. APPLICABLE WIRE SIZE AWG#30 (7/0.1)

Ø0.58 (CORE JACKET O. D.)

5	INSULATOR B	PBT (GF)	1		UL 94V-0 BLACK
4	CABLE HOUSING	PBT (GF)	2		UL 94V-0 BROWN
3	SHELL	STEEL	1	NICKEL PLATING	
2	INSULATOR A	PBT (GF)	1		UL 94V-0 BLACK
1	CONTACT	PHOSPHOR BRONZE	68	SEE NOTE 1	

LTR.	DATE	BY	REV. DESCRIPTION	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
	DATE Mar. 29, 2004		SCALE 2 / 1	UNIT mm (INCH)	3RD. A. P	HONDA TSUSHIN KOGYO CO., LTD.			
APP. DATE & REV.									
DR.	DE.	CHK.	CHK.	APP.	NAME	0.8mm SPACING FOR CABLE IDC MALE CONNECTOR			
Y. KATO	Y. KATO	—	C. NUNOKAWA	H. EBIHARA	PART NO.	HDRA-E () MA1+			REV.

HDRA-E68MA1	68	$0.8 \times 33 = 26.4$	31.95	28.2
HDRA-E36MA1	36	$0.8 \times 17 = 13.6$	19.16	15.4
PART No.	No. OF POS.	A	B	C

✱ UNDER
CONSIDERATION

ID= HDRA-E0MA1+ E0