




HONEYWELL PART NUMBER
412SX22-T
PRODUCT CODE VDX1225

REV	DOCUMENT	CHANGED BY	CHECK
8	0038558	SS 21MAY08	BLR



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 400°F
- 4 - MOVABLE CONTACT MATERIAL - 24K SOLID GOLD OVERLAY
- 5 - STATIONARY CONTACT MATERIAL - GOLD ALLOY

RELEASE NO.	PR-18199
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± 0.030 0.015 0.005			DRAWN	SPK	28FEB08	Honeywell				
OPERATING FORCE ----- 5 OZ MAX		CONTACT ARRANGEMENT SPDT						CHECK	RJ	28FEB08					
RELEASE FORCE ----- 1 OZ MIN		28 VOLTS DC RATING						THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL --- .003 MAX			SEA LEVEL	50,000 FT											
OVERTRAVEL ----- .004 MIN		INDUCTIVE	0.5 AMP	-	RESISTIVE	1 AMP	-								
		-			THIRD ANGLE PROJECTION 			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		APPROVALS	KEMA, CE	1A 250 V ~ T125 25E3 							B	I	412SX22-T		8
			UL, CSA	1A 125 VAC   BRAND				L22J			RASTER			SCALE	-