

COAXIAL CONNECTOR, BNO, X Ohm, Straight panel receptacle, jack (female), flange mount

23_BNO-0-0-2/133_N

Properties

- Used with balanced twin-conductor cables with 75 ohm to 130 ohm impedance
- Suitable for applications up to 200 MHz
- Ideal for computer networks and process control



Product configuration

Interface type	Gender	Standard
BNO	jack	IEC 60169-22

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	

Electrical data

Interface frequency	0.2 GHz
---------------------	---------

Mechanical data

Weight	0.0102 kg
Mating cycles	500
Flange type	square flange / 17.5 X 17.5
Tab style	solder end

Environmental data

Operation temperature	-50 °C ... 125 °C
-----------------------	-------------------

COAXIAL CONNECTOR, BNO, X Ohm, Straight panel receptacle, jack (female), flange mount

23_BNO-0-0-2/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22541085	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22541085	23_BNO-0-0-2/133_NE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2744 / Date of publication: 12.07.2025 / uncontrolled copy