




PRODUCT NUMBER

PITCH

HWxx50x300J0G

5.08 mm



Material:

- Item (a) Top body: Thermoplastic (UL94V-0)
- Item (b) Bottom body: Thermoplastic (UL94V-0)
- Item (c) Terminal lever: Thermoplastic (UL94V-0) Orange (RAL2011/P)
- Item (d) Spring clamp: Stainless Steel
- Item (e) Female contact: PhBz (CuSn) Tin plated
- Item (f) Flange screw: Steel Zinc plating M2.5 solt "+/-" combination type

Electrical cULus

- Voltage rating: 300V
- Current rating: 10A
- Solid wire (AWG): 12-26
- Stranded wire (AWG): 12-26
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus

Dimension
 DIM A = $N \times 5.08 + 0.5$
 DIM B = $(N-1) \times 5.08$
 DIM C = $(N-1) \times 5.08 + 10.16$
 DIM D = $(N-1) \times 5.08 + 15.24$
 N = Number of poles

POLES	Tolerance
2p-6p	± 0.20
7p-12p	± 0.30
13p-16p	± 0.40
17p-24p	± 0.50

PART NO.: HW xx 50 x 3 00J0 G

Solid block
 No. of poles
 02 2 poles
 03 3 poles
 ...
 24 24 poles

Color
 0 Black (RAL9005)
 2 Red (RAL3001/D)
 3 Orange (RAL2011/P)
 4 Yellow (RAL1018/A)
 5 Green (RAL6018/T)
 6 Blue (RAL5015/A)
 8 Grey (RAL7035/D)
 9 White (RAL1102)
 C Green (RAL6018/U)

RoHS compliant
 (lead < 4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		TERMINAL BLOCK			
					angles	$X \pm 0.5$	title TERMINAL BLOCK SPRING CLAMP, PLUGGABLE PLUG, WITH FLANGE CONTACT ON UP SIDE			
					$X \pm 1^\circ$	$X.X \pm 0.3$				
						$X.XX \pm 0.1$	scale			
					dr	EVIN ZHONG 051514	dwg no HWxx50x300J0G			
					enrg	EVIN ZHONG 051514				
					chr	HANKE FENG 051514	type CUSTOMER Drawing			
					appd	SHI JUN 051514				
sheet index	revision	A								