



**Circuit Board Indicators**

**Panel Mount Indicators**

**Solid State Lighting**

**Traffic Signals**

**Vehicle Lighting**

**Rail**

**Obstruction Lighting**

**Hazardous Area Lighting**

**Heliport Lighting**

**how to purchase**

[sales contacts](#)

[stock check](#)

[search](#)

[Product Line Search](#)

Please select a Product Line to search.

[Circuit Board Indicators](#)

[Find](#)

[Part # / Text Search](#)

**Part No.:**

**Text Search:**

[search](#)

[quick links](#)

**Dialight Corporate Video**

**Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp.** [View PDF File](#)

**Application Notes  
FAQs**

**Dialight Ltd (UK)**  
**Dialight Garufo**  
**Dialight BLP**  
**LumiDrives**

**Circuit Board Indicators - Through Hole Indicators**

P/N# **5530203400F**

**3 mm Lens**

Description	3 mm Bi-Level CBI
Package Options	50 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Bi-Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	2mA

**Absolute Maximum Ratings** (Ta = 25 °)


Solder Temp	<b>260° for 5 sec</b>
Operating Temp	<b>-40 to + 100° C</b>
Storage Temp	<b>-55 to +100° C</b>

**Distributor Stock Check**

**Check stock with our distributors now.**

5530203400F

[check stock](#)



RoHS / pB Free

[view PDF](#)

**Operating Characteristics**

LED Position	Found in position(s): 1	Found in position(s): 2
Color	Blank	Yellow
Lamp Type	Single Color	Single Color
LED Type		Low Current
Intensity Min (mcd)		2.3
Intensity Typ (mcd)		5.0
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)		75
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		