


**WDK 2.5 ZQV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

|            |                                                                                                                                                   |
|------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Multi-tier modular terminal, Screw connection, dark beige, 2.5 mm <sup>2</sup> , 400 V, Number of connections: 4, Number of levels: 2, TS 35, V-0 |
| Order No.  | <a href="#">1041100000</a>                                                                                                                        |
| Type       | WDK 2.5 ZQV                                                                                                                                       |
| GTIN (EAN) | 4008190972332                                                                                                                                     |
| Qty.       | 100 ST                                                                                                                                            |

## Technical data

### Approvals

Approvals



|                       |                            |
|-----------------------|----------------------------|
| ROHS                  | Conform                    |
| UL File Number Search | <a href="#">UL Website</a> |
| Certificate No. (UR)  | E60693                     |

### Dimensions and weights

|                          |             |                |             |
|--------------------------|-------------|----------------|-------------|
| Depth                    | 62.5 mm     | Depth (inches) | 2.4606 inch |
| Depth including DIN rail | 63 mm       | Height         | 69 mm       |
| Height (inches)          | 2.7165 inch | Width          | 5.1 mm      |
| Width (inches)           | 0.2008 inch | Net weight     | 11.78 g     |

### Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C         | Continuous operating temp., max. | 130 °C        |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

### Rating data IECEx/ATEX

|                                |                   |                                 |                   |
|--------------------------------|-------------------|---------------------------------|-------------------|
| Certificate No. (ATEX)         | DEMKO15ATEX1346U  | Certificate No. (IECEx)         | IECExULD15.0003U  |
| Max. voltage (ATEX)            | 275 V             | Current (ATEX)                  | 21 A              |
| Wire cross section max. (ATEX) | 4 mm <sup>2</sup> | Max. voltage (IECEx)            | 275 V             |
| Current (IECEx)                | 21 A              | Wire cross section max. (IECEx) | 4 mm <sup>2</sup> |
| Marking EN 60079-7             | Ex eb II C Gb     | Ex 2014/34/EU label             | II 2 G D          |

### System specifications

|                                     |                                                                          |                               |     |
|-------------------------------------|--------------------------------------------------------------------------|-------------------------------|-----|
| Version                             | Screw connection, for plug-in cross-connector, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 2                                                                        | Number of levels              | 2   |
| Number of clamping points per level | 2                                                                        | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No                                                                       | PE connection                 | No  |
| Rail                                | TS 35                                                                    | N-function                    | No  |
| PE function                         | No                                                                       | PEN function                  | No  |

## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## 2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

|                                                                                                            |                     |                                                                                                            |                     |
|------------------------------------------------------------------------------------------------------------|---------------------|------------------------------------------------------------------------------------------------------------|---------------------|
| Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, max. | 1.5 mm <sup>2</sup> | Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, min. | 0.5 mm <sup>2</sup> |
| Wire cross-section, finely stranded, two clampable wires, max.                                             | 1.5 mm <sup>2</sup> | Wire connection cross section, finely stranded, two clampable wires, min.                                  | 0.5 mm <sup>2</sup> |

## Additional technical data

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Open sides               | right | Number of similar terminals | 1       |
| Explosion-tested version | Yes   | Type of mounting            | Snap-on |

## CSA rating data

|                               |        |                       |           |
|-------------------------------|--------|-----------------------|-----------|
| Wire cross section max. (CSA) | 12 AWG | Voltage size C (CSA)  | 300 V     |
| Current size C (CSA)          | 25 A   | Certificate No. (CSA) | 12400-391 |
| Wire cross section min. (CSA) | 26 AWG |                       |           |

## Conductors for clamping (additional connection)

|                                        |                  |
|----------------------------------------|------------------|
| Connection type, additional connection | Screw connection |
|----------------------------------------|------------------|

## Conductors for clamping (rated connection)

|                                                                                         |                      |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|---------------------|
| Gauge to IEC 60947-1                                                                    | A3                   | Wire connection cross section AWG, max.                                                 | AWG 12              |
| Connection direction                                                                    | on side              | Tightening torque, max.                                                                 | 0.6 Nm              |
| Tightening torque, min.                                                                 | 0.4 Nm               | Stripping length                                                                        | 10 mm               |
| Type of connection 2                                                                    | Screw connection     | Type of connection                                                                      | Screw connection    |
| Number of connections                                                                   | 4                    | Clamping range, max.                                                                    | 4 mm <sup>2</sup>   |
| Clamping range, min.                                                                    | 0.05 mm <sup>2</sup> | Clamping screw                                                                          | M 2.5               |
| Blade size                                                                              | 0.6 x 3.5 mm         | Wire connection cross section AWG, min.                                                 | AWG 30              |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Connection cross-section, stranded, max.                                                | 4 mm <sup>2</sup>    | Connection cross-section, stranded, min.                                                | 1.5 mm <sup>2</sup> |
| Torque level with DMS electric screwdriver                                              | 1                    | Wire connection cross-section, solid core, max.                                         | 4 mm <sup>2</sup>   |
| Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup>  |                                                                                         |                     |

## Dimensions

|              |         |
|--------------|---------|
| TS 35 offset | 35.5 mm |
|--------------|---------|

## General

|                                         |               |                                         |        |
|-----------------------------------------|---------------|-----------------------------------------|--------|
| Wire connection cross section AWG, max. | AWG 12        | Wire connection cross section AWG, min. | AWG 30 |
| Standards                               | IEC 60947-7-1 | Rail                                    | TS 35  |

## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rating data

|                                              |                     |                                 |               |
|----------------------------------------------|---------------------|---------------------------------|---------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 400 V         |
| Rated DC voltage                             | 400 V               | Rated current                   | 24 A          |
| Current at maximum wires                     | 32 A                | Standards                       | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 6 kV          |
| Power loss in accordance with IEC 60947-7-x  | 0.77 W              | Pollution severity              | 3             |


## UL rating data

|                                         |        |                                         |        |
|-----------------------------------------|--------|-----------------------------------------|--------|
| Voltage size B (UR)                     | 300 V  | Current size B (UR)                     | 20 A   |
| Conductor size Factory wiring max. (UR) | 12 AWG | Current size C (UR)                     | 20 A   |
| Voltage size C (UR)                     | 300 V  | Conductor size Factory wiring min. (UR) | 22 AWG |
| Certificate No. (UR)                    | E60693 | Conductor size Field wiring min. (UR)   | 22 AWG |
| Conductor size Field wiring max. (UR)   | 12 AWG |                                         |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0    | EC000897    |
| ETIM 8.0    | EC000897    | ETIM 9.0    | EC000897    |
| ETIM 10.0   | EC000897    | ECLASS 9.0  | 27-14-11-20 |
| ECLASS 9.1  | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |
| ECLASS 13.0 | 27-25-01-02 | ECLASS 14.0 | 27-25-01-02 |
| ECLASS 15.0 | 27-25-01-02 |             |             |

## Drawings



## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5 mm<sup>2</sup>


End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | WAP WDK2.5                 | Version                                                            |
| Order No.  | <a href="#">1059100000</a> | End plate for terminals, dark beige, Height: 69 mm, Width: 1.5 mm, |
| GTIN (EAN) | 4008190101954              | V-0, Wemid, Snap-on: No                                            |
| Qty.       | 20 ST                      |                                                                    |
| Type       | WAP WDK2.5 BL              | Version                                                            |
| Order No.  | <a href="#">1059180000</a> | End plate for terminals, blue, Height: 69 mm, Width: 1.5 mm, V-0,  |
| GTIN (EAN) | 4008190081089              | Wemid, Snap-on: No                                                 |
| Qty.       | 20 ST                      |                                                                    |

## W-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

## General ordering data

|            |                            |                                                                     |
|------------|----------------------------|---------------------------------------------------------------------|
| Type       | WTW EN                     | Version                                                             |
| Order No.  | <a href="#">1058800000</a> | Partition plate (terminal), dark beige, Height: 86 mm, Width: 3 mm, |
| GTIN (EAN) | 4008190140175              | V-0, Wemid                                                          |
| Qty.       | 20 ST                      |                                                                     |
| Type       | WEW 35/2                   | Version                                                             |
| Order No.  | <a href="#">1061200000</a> | End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C      |
| GTIN (EAN) | 4008190030230              |                                                                     |
| Qty.       | 50 ST                      |                                                                     |
| Type       | WAD 4 GE BED               | Version                                                             |
| Order No.  | <a href="#">1072000000</a> | Terminal cover, yellow, PA 66, Height: 19.8 mm, Width: 4.5 mm,      |
| GTIN (EAN) | 4008190446109              | Depth: 9.6 mm, V-2                                                  |
| Qty.       | 50 ST                      |                                                                     |
| Type       | WAD 4 WS                   | Version                                                             |
| Order No.  | <a href="#">1072100000</a> | Terminal cover, white, PA 66, Height: 19.8 mm, Width: 4.5 mm,       |
| GTIN (EAN) | 4008190446116              | Depth: 9.6 mm, V-2                                                  |
| Qty.       | 50 ST                      |                                                                     |

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.


Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | DEK 5/5 MC NE WS           | Version                                                           |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00         |
| GTIN (EAN) | 4008190397111              | Weidmueller, white                                                |
| Qty.       | 1000 ST                    |                                                                   |
| Type       | WS 8/5 MC NE WS            | Version                                                           |
| Order No.  | <a href="#">1640740000</a> | WS, Terminal marker, 8 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4008190279103              | Allen-Bradley, white                                              |
| Qty.       | 720 ST                     |                                                                   |

## Shielding connection



With the LS 2.8 WDU2.5-10, many feed-through modular terminal blocks from the W series can be converted very easily. Inserting the LS 2.8 WDU2.5-10 allows the cable shielding braid to be looped through directly at the terminal block by soldering or using a suitable flat cable lug.

## General ordering data

|            |                            |                      |
|------------|----------------------------|----------------------|
| Type       | LS 2.8 WDU2.5-10           | Version              |
| Order No.  | <a href="#">1056400000</a> | W-Series, Shield bus |
| GTIN (EAN) | 4008190036454              |                      |
| Qty.       | 100 ST                     |                      |

## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

2.5 mm<sup>2</sup>

2.5  
mm<sup>2</sup>

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | ZQV 2.5N/10                | Version                                                               |
| Order No.  | <a href="#">1527690000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447989              | 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm             |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/10 BL             | Version                                                               |
| Order No.  | <a href="#">1527880000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 10, |
| GTIN (EAN) | 4050118448573              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/10 RD             | Version                                                               |
| Order No.  | <a href="#">2108910000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 10,  |
| GTIN (EAN) | 4050118486018              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/2                 | Version                                                               |
| Order No.  | <a href="#">1527540000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448467              | 2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm               |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/2 BL              | Version                                                               |
| Order No.  | <a href="#">1527740000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 2,  |
| GTIN (EAN) | 4050118448658              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/2 RD              | Version                                                               |
| Order No.  | <a href="#">2108470000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 2,   |
| GTIN (EAN) | 4050118448542              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/20                | Version                                                               |
| Order No.  | <a href="#">1527720000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447972              | 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/20 BL             | Version                                                               |
| Order No.  | <a href="#">1527890000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 20, |
| GTIN (EAN) | 4050118448566              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/20 RD             | Version                                                               |
| Order No.  | <a href="#">2108920000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 20,  |
| GTIN (EAN) | 4050118485899              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/3                 | Version                                                               |
| Order No.  | <a href="#">1527570000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448450              | 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                |
| Qty.       | 60 ST                      |                                                                       |



## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | ZQV 2.5N/3 BL              | Version                                                               |
| Order No.  | <a href="#">1527770000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 3,  |
| GTIN (EAN) | 4050118448641              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                   |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/3 RD              | Version                                                               |
| Order No.  | <a href="#">2108690000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 3,   |
| GTIN (EAN) | 4050118448535              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                   |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/4                 | Version                                                               |
| Order No.  | <a href="#">1527590000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448443              | 4, Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm              |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/4 BL              | Version                                                               |
| Order No.  | <a href="#">1527780000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 4,  |
| GTIN (EAN) | 4050118448634              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                 |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/4 RD              | Version                                                               |
| Order No.  | <a href="#">2108700000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 4,   |
| GTIN (EAN) | 4050118448528              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                 |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/5                 | Version                                                               |
| Order No.  | <a href="#">1527620000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448436              | 5, Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/5 BL              | Version                                                               |
| Order No.  | <a href="#">1527790000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 5,  |
| GTIN (EAN) | 4050118448627              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/5 RD              | Version                                                               |
| Order No.  | <a href="#">2108710000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 5,   |
| GTIN (EAN) | 4050118448511              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/50                | Version                                                               |
| Order No.  | <a href="#">1527730000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118411362              | 50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm              |
| Qty.       | 5 ST                       |                                                                       |
| Type       | ZQV 2.5N/50 BL             | Version                                                               |
| Order No.  | <a href="#">1527920000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 50, |
| GTIN (EAN) | 4050118448559              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 ST                       |                                                                       |
| Type       | ZQV 2.5N/50 RD             | Version                                                               |
| Order No.  | <a href="#">2109000000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 50,  |
| GTIN (EAN) | 4050118486001              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 ST                       |                                                                       |
| Type       | ZQV 2.5N/6                 | Version                                                               |
| Order No.  | <a href="#">1527630000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448429              | 6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/6 BL              | Version                                                               |
| Order No.  | <a href="#">1527820000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 6,  |
| GTIN (EAN) | 4050118448610              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 ST                      |                                                                       |

## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                      |
|------------|----------------------------|----------------------------------------------------------------------|
| Type       | ZQV 2.5N/6 RD              | Version                                                              |
| Order No.  | <a href="#">2108720000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 6,  |
| GTIN (EAN) | 4050118448504              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/7                 | Version                                                              |
| Order No.  | <a href="#">1527640000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:  |
| GTIN (EAN) | 4050118448412              | 7, Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm             |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/7 BL              | Version                                                              |
| Order No.  | <a href="#">1527830000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 7, |
| GTIN (EAN) | 4050118448603              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/7 RD              | Version                                                              |
| Order No.  | <a href="#">2108810000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 7,  |
| GTIN (EAN) | 4050118448498              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/8                 | Version                                                              |
| Order No.  | <a href="#">1527670000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:  |
| GTIN (EAN) | 4050118448405              | 8, Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm             |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/8 BL              | Version                                                              |
| Order No.  | <a href="#">1527840000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 8, |
| GTIN (EAN) | 4050118448597              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/8 RD              | Version                                                              |
| Order No.  | <a href="#">2108870000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 8,  |
| GTIN (EAN) | 4050118448481              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/9                 | Version                                                              |
| Order No.  | <a href="#">1527680000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:  |
| GTIN (EAN) | 4050118447996              | 9, Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm             |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/9 BL              | Version                                                              |
| Order No.  | <a href="#">1527870000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 9, |
| GTIN (EAN) | 4050118448580              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/9 RD              | Version                                                              |
| Order No.  | <a href="#">2108900000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 9,  |
| GTIN (EAN) | 4050118448474              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                |
| Qty.       | 20 ST                      |                                                                      |

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 ST                     |                            |
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 ST                     |                            |

## WS 8/5



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

|            |                            |                                                   |
|------------|----------------------------|---------------------------------------------------|
| Type       | WS 8/5 MM WS               | Version                                           |
| Order No.  | <a href="#">2007150000</a> | WS, Terminal marker, 8 x 5 mm, Weidmueller, white |
| GTIN (EAN) | 4050118392029              |                                                   |
| Qty.       | 800 ST                     |                                                   |

## W-Series



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## WDK 2.5 ZQV

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany


www.weidmueller.com

## Accessories

## General ordering data

|            |                            |                                              |
|------------|----------------------------|----------------------------------------------|
| Type       | WTA 4N/ZA WDK 2.5          | Version                                      |
| Order No.  | <a href="#">1879350000</a> | Test adapter (terminal), 1.5 mm², 250 V, 6 A |
| GTIN (EAN) | 4032248503261              |                                              |
| Qty.       | 25 ST                      |                                              |

## Test plugs




Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |                                       |
|------------|----------------------------|---------------------------------------|
| Type       | PS_ZQV                     | Version                               |
| Order No.  | <a href="#">1121740000</a> | Test adapter (terminal), 1000 V, 20 A |
| GTIN (EAN) | 4032248902675              |                                       |
| Qty.       | 1 ST                       |                                       |
| Type       | PS_ZQV_SET                 | Version                               |
| Order No.  | <a href="#">1116710000</a> | Test adapter (terminal), 1000 V, 20 A |
| GTIN (EAN) | 4032248911455              |                                       |
| Qty.       | 1 ST                       |                                       |

## W-Series



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

|            |                            |                                              |
|------------|----------------------------|----------------------------------------------|
| Type       | WTA 4N WDK 2.5             | Version                                      |
| Order No.  | <a href="#">1878660000</a> | Test adapter (terminal), 1.5 mm², 250 V, 6 A |
| GTIN (EAN) | 4032248503285              |                                              |
| Qty.       | 25 ST                      |                                              |
| Type       | WZR WDK2.5                 | Version                                      |
| Order No.  | <a href="#">1074000000</a> | W-Series, Intermediate frame                 |
| GTIN (EAN) | 4008190890384              |                                              |
| Qty.       | 20 ST                      |                                              |