

SACC-M12FS-12SOL-PG 9-M SH - Connector



1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 12-position, shielded, Socket straight M12, coding: A, Solder connection, knurl material: Zinc die-cast, nickel-plated, cable gland Pg9, external cable diameter 6 mm ... 8 mm

Your advantages

- Safe use in the field, thanks to a high degree of protection
- Save space – with high-pos. connectors
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

Item number	1404411
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF2
Product key	AF2CGA
GTIN	4046356693844
Weight per piece (including packing)	45.68 g
Weight per piece (excluding packing)	45.68 g
Customs tariff number	85366990
Country of origin	DE

SACC-M12FS-12SOL-PG 9-M SH - Connector



1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------------	---


Product properties

Product type	Circular connector (cable-side)
Sensor type	Universal
Number of positions	12
No. of cable outlets	1
Shielded	yes
Coding	A
Cable outlet	straight
Pg screw connection	Pg9

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Dimensional drawing	
Width	19.6 mm
Height	19.6 mm
Length	56 mm

External dimensions

Outside diameter	6 mm ... 8 mm
------------------	---------------

Housing

Diameter housing	19.6 mm
------------------	---------

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	Zinc die-cast, nickel-plated
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material for screw connection	Zinc die-cast, nickel-plated

SACC-M12FS-12SOL-PG 9-M SH - Connector



1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Connection data

Conductor connection

Connection method	Solder connection
Connection cross section	0.08 mm ² ... 0.25 mm ² (without ferrule)
	0.08 mm ² ... 0.25 mm ² (solid)
Connection cross section AWG	28 ... 24 (without ferrule)
Stripping length of the individual wire	4 mm
Tightening torque	0.4 Nm (M12 knurl)
	0.8 Nm ... 1 Nm (Pressure screw)

Electrical properties

Rated surge voltage	0.5 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	> 10 GΩ
Nominal voltage U _N	30 V AC
	30 V DC
Nominal current I _N	1.5 A (up to 40 °C)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	A

Cable/line

Signal type/category	Universal
Stripping length of the individual wire	4 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C (Plug / socket)

Standards and regulations

M12

Standard designation	M12 connector
----------------------	---------------

SACC-M12FS-12SOL-PG 9-M SH - Connector



1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Standards/specifications	IEC 61076-2-101
--------------------------	-----------------

SACC-M12FS-12SOL-PG 9-M SH - Connector




1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Drawings

Dimensional drawing




M12 x 1 socket, straight, shielded

1404411


<https://www.phoenixcontact.com/ae/products/1404411>

Functional drawing

Assembly steps for M 12 male/female connector and conductor




Slide parts onto the conductor



¹⁾ For straight version: 35

Strip conductor, widen shield and lay around the shielding ring, cut off projecting mesh.



Slide cores through the housing, mount shielding ring, gasket and clamping cage. Tighten pressure screw to fix the cable. Screw down cores, mount male/female connector part and tighten pressure screw.


SACC-M12FS-12SOL-PG 9-M SH - Connector

1404411

<https://www.phoenixcontact.com/ae/products/1404411>



Schematic diagram



Pin assignment M12 socket, 12-pos., A-coded, view female side

SACC-M12FS-12SOL-PG 9-M SH - Connector



1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/ae/products/1404411>

 cUL Recognized Approval ID: FILE E 221474				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	30 V	1 A	-	-

 UL Recognized Approval ID: FILE E 221474				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	30 V	1 A	-	-

SACC-M12FS-12SOL-PG 9-M SH - Connector



1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-M12FS-12SOL-PG 9-M SH - Connector



1404411

<https://www.phoenixcontact.com/ae/products/1404411>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d08ccea1-0fc3-488a-a11c-dbe81594dac9

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com