



Part Number : [2132740001](#)

Product Description : PowerPlane BusBar Assembly, Middle Size, Vertical Mount, Single Hole, Open Side Walls, Silver (Ag) Plated

Series Number : 213274

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2132740001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


Specifications

[2132740001-AS-000.pdf](#)

[2132740001-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	213274
Description	PowerPlane BusBar Assembly, Middle Size, Vertical Mount, Single Hole, Open Side Walls, Silver (Ag) Plated
Application	Power
Component Type	PCB Receptacle
Product Name	PowerPlane
UPC	195842626768

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	1000V

Physical

Circuits (Loaded)	1
-------------------	---

Circuits (maximum)	1
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	10.028/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw

This document was generated on May 04, 2026