






PRODUCT NUMBER	PITCH
V7xx71x100J0G	5.00 mm



RECOMMENDED P.C.B. LAYOUT
TOP VIEW



SECTION P-P

Material:

- Item①Terminal body:Thermoplastic (UL94V-0)
- Item②Female contact:PhBz(CuSn), Tin plated
- Item③Terminal cover:Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

PART NO.: V7 xx 7 1 x 1 00J0 G

DIM		TOL				
		2P-5P	6P-10P	11P-15P	16P-20P	21P-24P
Dim L	N×5.0+2.0	±0.15	±0.20	±0.25	±0.30	±0.40
Dim B	(N-1)×5.0	±0.15	±0.20	±0.25	±0.30	±0.40
Dim C	N×5.0	0 -0.20		0 -0.30		
Dim D	(N-1)×5.0	±0.15	±0.20	±0.25	±0.30	±0.40

Solid block
No. of poles
02 2poles
03 3poles
...
24 24poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	TERMINAL BLOCK			
					angles		title			
					pos		TERMINAL BLOCK			
					flat		PLUGGABLE PCB PLUG,RIGHT ANGLE			
					X'±1"		scale			
					dr	EVIN ZHONG 043014	FCI			
					enrg	EVIN ZHONG 043014	dwg no			
					chr	HANKE FENG 043014	sheet 1 of 1 size			
					appd	SHI JUN 043014	V7xx71x100J0G A4			
sheet index				revision	A		type			
				sheet	1		CUSTOMER Drawing			