





Raychem
PART NO.
MTC100-JA2-S11-T14
DATE CODE



△ WEIGHT (MAX.): $\frac{\text{LBS}}{.0109} \mid \frac{\text{GRAMS}}{4.94}$

△ SOCKET ONE: SOCKET NUMBER ONE MARKED IN CONTRASTING COLOR.

3. WAFER: WAFER MEETS THE REQUIREMENTS OF RAYCHEM SPECIFICATION D-6012.

2. FINISH: 2-A SOCKET WAFER; FINISH TO BE AS MOLDED.
2-B SOCKET CONTACT; GOLD PLATE PER MIL-G-45204 CLASS I.
(ENGAGING END)
2-C CONTACT TAIL; COATED WITH SOLDER PER QQ-S-571.

1. MATERIAL: 1-A SOCKET WAFER; HIGH GRADE POLYARYLENE THERMO-PLASTIC.
1-B SOCKET CONTACT; COPPER ALLOY PER QQ-B-750 (A).
1-C SOLDERPAK® TERMINATORS ASSY; REFER TO RAYCHEM DWG. CTA-0036 FOR DATA.

NOTES

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES BRACKETED DIMENSIONS () ARE METRIC AND TOLERANCES ARE: XXX: $\pm .005$ (0.13 M.M.) XX: $\pm .02$ (0.51 M.M.) X: $\pm .01$	DRAWN	W.V.J.	1-15-81	Raychem RAYCHEM CORPORATION 3300 EAST 17TH AVENUE DENVER, COLORADO 80202		
	CHECKED					
	APPROVED			TITLE KIT, 2" SOCKET WAFER "A" WITH SOLDERPAK® TERMINATORS, FOR ROUND WIRE (20-26 AWG) 125 °C TEMPERATURE RATING MTC 100 SERIES		
	APPROVED					
	APPROVED					
	SIZE	CODE IDENT	DWG. NO.			
	A	NO. 06090	MTC100-JA2-S11-T14			
DO NOT SCALE THIS DRAWING				WEIGHT	△	SHEET 1 OF 1