
All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon



Raspberry Pi Compute Module 4 4GB/32GB Wi-Fi (Pre-order)

SKU:DFR0775 Brand:Raspberry Pi Reward Points: 650

* Model: 1GB/Lite | 2GB/Lite Wi-Fi | 2GB/8GB Wi-Fi | 2GB/32GB Wi-Fi | 4GB/32GB Wi-Fi | CM4 IO Expansion Carrier | CM4 Gigabit Router Carrier

Quantity: - +

ADD TO CART

Frequently Bought Together

Raspberry Pi Compute Module 4 4GB/32GB Wi-Fi (Pre-order) + Raspberry ... Version) + Raspberry Pi 4 Model + Raspberry Pi... Board + Raspbe... Antenna Kit =

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

Note: This product is under the status of Pre-order, will be shipped at the end of April.

Raspberry Pi Compute Module 4 harnesses the computing power of the popular Raspberry Pi 4 Model B, bringing it to a smaller form factor suitable for integration into products.

This version of the Raspberry Pi Compute Module 4 includes a high-performance 64-bit quad-core processor, 4GB LPDDR4 RAM, 32GB eMMC, dual-display support at resolutions up to 4K, hardware video decode at up to 4Kp60, Gigabit Ethernet, USB 2.0, dual camera interfaces, PCIe Gen 2 x1 interface, and dual-band 2.4/5.0GHz wireless LAN and Bluetooth 5.0.

The dual-band 2.4/5.0GHz wireless LAN and Bluetooth 5.0 have modular compliance certification. This allows the board to be designed into end products with significantly reduced compliance testing, improving both cost and time to market. Either the onboard antenna or an external antenna kit can be used.

Hardware Overview

RPI Compute Module 4 Hardware Overview

Dimensions

Downloaded from Arrow.com.



Note:

- 4 x M2.5 holes in corners
- All dimensions are in mm

FEATURES

- High-performance 64-bit quad-core processor
- Dual display support at resolutions up to 4K
- Hardware video decode at up to 4Kp60
- Dual camera interfaces
- PCIe Gen 2 x1 interface

SPECIFICATION

- Processor: Broadcom BCM2711 quad-core Cortex-A72 (ARM v8) 64-bit SoC @ 1.5GHz
- Memory: 4GB LPDDR4
- Storage: 32GB eMMC
- Connectivity: Optional wireless LAN, 2.4GHz and 5.0GHz IEEE 802.11b/g/n/ac wireless, Bluetooth 5.0, BLE with onboard and external antenna options

    1 × USB 2.0 interface
    PCIe Gen 2 x1 interface
    28 GPIO signals
    SD card interface for SD card or external eMMC (for use only with Compute Module 4 variants without eMMC)

- Video: Dual HDMI interface (up to 4Kp60 supported)

    2-lane MIPI DSI display interface
    2-lane MIPI CSI camera interface
    4-lane MIPI DSI display interface
    4-lane MIPI CSI camera interface

- Multimedia: H.265 (4Kp60 decode); H.264 (1080p60 decode, 1080p30 encode); OpenGL ES 3.0 graphics
- Input power: 5V DC
- Operating temperature: 0 to +80°C
- Dimensions: 55 mm × 40 mm
- Production lifetime: Raspberry Pi Compute Module 4 will remain in production until at least January 2028

DOCUMENTS

Downloaded from Arrow.com.

- Raspberry Pi Compute Module 4 product brief
- Raspberry Pi Compute Module 4 datasheet
- Compute Module 4 STEP file
- Compute Module 4 Lite (without eMMC) STEP file

SHIPPING LIST

- Raspberry Pi Compute Module 4 4GB/32GB Wi-Fi ×1

REVIEW

FAQ

0 Comments DFRobot Disqus' Privacy Policy Login
Recommend Tweet Share Sort by Best
ırt the discussion...
Be the first to comment.
Subscribe Add Disqus to your site Do Not Sell My Data DISQUS

Sign up for exclusive offers!

Your email address →

Like us on

Downloaded from Arrow.com.