


Data Sheet | Item Number: 788-515


Relay module; Nominal input voltage: 115 VAC; 2 changeover contacts; Limiting continuous current: 8 A; Red status indicator; Module width: 15 mm; 2,50 mm²; gray

<https://www.wago.com/788-515>




Color: ■ gray



Similar to illustration



DC load limit curve



Current-carrying capacity curve



Notes	
Safety Information	A separator plate (e.g., 209-191) must be used for voltages exceeding 250 V between adjacent relay modules and to comply with reinforced insulation requirements.
Note	Reinforced insulation between coil and contacts To protect the relay coils and contacts, inductive loads must be dampened with an effective protection circuit.

Technical data	
Control circuit	Load circuit
Nominal input voltage U _N	115 VAC
Input voltage range	±10 %
Nominal input current at U _N	8 mA
	Number of changeover/switchover contacts 2
	Contact material (relay) AgNi 90/10
	Limiting continuous current 8 A
	Inrush current (resistive) max. (AC) 15 A / 4 s
	Switching Voltage, Max. 250 VAC
	Switching power (resistive) max. AC 2000 VA; DC (see load limit curve)
	Utilization category AC-15: 3 A / 250 VAC DC-13: 2 A / 24 VDC
	Recommended minimum load 12 V / 10 mA
	Pull-in time (typ.) 10 ms
	Drop-out time (typ.) 35 ms
	Bounce time (typ.) 10 ms
	Electrical life (NO; resistive load; 23 °C) 10 x 10 ³ switching operations
	Mechanical life 30 x 10 ⁶ switching operations
	Switching frequency with/without load (max.) 6 min ⁻¹ / 1200 min ⁻¹

Signaling	
Status indicator	Red LED

Safety and protection	
Rated Voltage	250 V
Rated impulse withstand voltage	4 kV
Pollution degree	3
Dielectric strength (control/load circuit) (AC, 1 min)	5 kVrms
Dielectric strength (open contact) (AC, 1 min)	1 kVrms
Dielectric strength (load/load circuit) (AC, 1 min)	2.5 kVrms
Safety Information	A separator plate (e.g., 209-191) must be used for voltages exceeding 250 V between adjacent relay modules and to comply with reinforced insulation requirements.
Protection type	IP20

Connection Data	
Connection technology	Push-in CAGE CLAMP®
Solid conductor	0.34 ... 2.5 mm² / 22 ... 14 AWG
Fine-stranded conductor	0.34 ... 2.5 mm² / 22 ... 14 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches



Physical data		
Width		15 mm / 0.591 inches
Height		86 mm / 3.386 inches
Depth from upper-edge of DIN-rail		54 mm / 2.126 inches

Mechanical data		
Mounting type		DIN-35 rail

Material data		
Note (material data)		Information on material specifications can be found here
Color		gray
Fire load		0.763 MJ
Weight		45 g

Environmental requirements		
Ambient temperature (operation at U _N)		-40 ... +70 °C
Ambient temperature UL (operation at U _N)		-40 ... +50 °C
Ambient temperature (storage)		-40 ... +70 °C
Processing temperature		-25 ... +50 °C
Temperature range of connection cable		≥ (T _{ambient} + 20 K)

Standards and Specifications		
Standards/specifications		EN 61010-2-201 EN 61810-1 EN 61373 UL 508 DNV

Basic relay		
WAGO Basic Relay		788-176

Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
PU (SPU)		20 (1) pcs
Packaging type		Box
Country of origin		CN
GTIN		4045454389512
Customs tariff number		85364900990

Product Classification		
UNSPSC		39122334
eCl@ss 10.0		27-37-16-01
eCl@ss 9.0		27-37-16-01
ETIM 9.0		EC001437
ETIM 10.0		EC001437
ECCN		NO US CLASSIFICATION



Environmental Product Compliance	
CAS-No.	7439-92-1 79-94-7
REACH Candidate List Substance	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol Lead
RoHS Compliance Status	Compliant, No Exemption
SCIP notification number (Austria)	0e6d74ce-5e67-4e11-8023-a1a3282aced4
SCIP notification number (Belgium)	db223fa3-5c11-4613-9518-0e2cede2f9ed
SCIP notification number (Bulgaria)	503e07b0-4c98-4014-8cd3-bc97b2795814
SCIP notification number (Czech Republic)	fe2dd327-e009-4cdc-b377-9f80deb526dc
SCIP notification number (Denmark)	61f86245-0081-4e8f-a75e-13c213ec011c
SCIP notification number (Finland)	7363e2f4-4d82-4253-8078-ef4b736e7938
SCIP notification number (France)	39e55559-6d30-4698-94fc-2524a94bd493
SCIP notification number (Germany)	dba5ee34-f538-4db4-96f8-bc987bf55ff4
SCIP notification number (Hungary)	2499a617-65f5-43a2-966f-1b7394ba55da
SCIP notification number (Italy)	f3b77661-6d29-4916-bdec-7eff019debe6
SCIP notification number (Netherlands)	9f2a52e9-0fa4-444d-9bbd-77b88a424950
SCIP notification number (Poland)	c0ec70f9-9b55-4f6f-b88c-fbe5db6c8e2c
SCIP notification number (Romania)	c6ad885f-4d91-4441-a171-38637e3dd903
SCIP notification number (Sweden)	68252eaf-9b7f-449f-b449-f2bb060d06d5

Approvals / Certificates		
General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03084
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 508	E175199 Vol.1 Sec.6
Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Approvals for marine applications		
		
Approval	Standard	Certificate Name
DNV DNV Germany GmbH	DNV-CG-0339, Aug. 2021	TAA00001D1

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 788-515

↓

Documentation			
Bid Text		Instruction Leaflet	
788-515	19.02.2019	xml 4.60 KB	↓
788-515	25.01.2019	docx 16.42 KB	↓
		Sockets with Elementary Relay/ SSR	V 1.0.1 09.10.2020
		pdf	2271.22 KB
			↓

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 788-515	EPLAN Data Portal 788-515
↓	↓
	WSCAD Universe 788-515
	↓
	ZUKEN Portal 788-515
	↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Basic relay

1.1.1.1 Basic relay



Item No.: 788-176
Basic relay; Nominal input voltage: 115 VAC; 2 changeover contacts; Limiting continuous current: 8 A; Module width: 13 mm; Module height: 15 mm

1.1.2 Ferrule

1.1.2.1 Ferrule



Item No.: 216-241
Ferrule; Sleeve for 0.5 mm² / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white

Item No.: 216-242
Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

Item No.: 216-243
Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red

Item No.: 216-244
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black



Item No.: 216-542
Twin ferrule; Sleeve for 2 x 1 mm² / AWG 2 x 18; red, insulated; 12 mm long; red

1.1.3 Filter module

1.1.3.1 Suppressor module



Item No.: 788-148
Filter module; RC filter element; Nominal voltage: 230 VAC

1.1.4 Indicators

1.1.4.1 Status indication



Item No.: 788-124
Accessories for relay modules; Operation status indicator: red; Nominal operating voltage: 115 VAC

1.1.5 Jumper

1.1.5.1 Jumper



Item No.: 788-118
Jumper; for jumper slot; 2-way; from 1 to 3; insulated; light gray



Item No.: 788-113
Jumper; for jumper slot; 2-way; insulated; light gray



Item No.: 859-402
Jumper; for jumper slot; 2-way; insulated; light gray



Item No.: 788-114
Jumper; for jumper slot; 3-way; insulated; light gray



Item No.: 788-115
Jumper; for jumper slot; 4-way; insulated; light gray



Item No.: 788-116
Jumper; for jumper slot; 6-way; insulated; light gray



Item No.: 788-117
Jumper; for jumper slot; 8-way; insulated; light gray

1.1.6 Marking

1.1.6.1 Double marker carrier



Item No.: 209-128
Adaptor; gray

1.1.6.2 Group marker carrier



Item No.: 249-105
Group marker carrier; gray



Item No.: 209-145
Group marker carrier; white

1.1.6.3 Marker



Item No.: 209-183
Marker; white

Item No.: 793-502
WMB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type; white

Item No.: 793-503
WMB marking card; as card; MARKED; 11 ... 20 (10x); not stretchable; Horizontal marking; snap-on type; white

Item No.: 793-504
WMB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Horizontal marking; snap-on type; white



Item No.: 793-505
WMB marking card; as card; MARKED; 31 ... 40 (10x); not stretchable; Horizontal marking; snap-on type; white

Item No.: 793-501
WMB marking card; as card; not stretchable; plain; snap-on type; white

Item No.: 2009-115
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.6.4 Marking device



Item No.: 210-110
Fiber-tip pen

1.1.6.5 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

1.1.6.6 Protective marker cover



Item No.: 209-184
Protection cover; transparent

1.1.7 Tool


1.1.7.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured


Installation Notes

Conductor termination



Conductor termination

Commoning



Easy commoning using adjacent jumpers

Marking



Marking using WMB Multi markers and group marker carriers.