



PentaMag

Multiband GSM/3G
Magnetic Antenna

Features

- ◆ Magnetic Mount
- ◆ Covers Cellular, GSM and 3G bands
- ◆ SMA-Male or FME-Female connector
- ◆ Ideal for multiband terminals

Specifications

Specifications	
Radiating element	1/4 Wave Element
Frequency range	824-960/1710-2170 MHz
Peak gain	2.0 dBi
Polarisation	Linear
Return loss	< -7 dB
Power rating	10W
Cable / Connector	3M RG-174 and SMA-Male or FME-Female connector
Dimensions	87 x 27mm (length x diameter at base excluding connector)

Popular Ordering Options

FMA35153-SM-3K	PentaMag with 3M RG-174 and SMA-Male
FMA35153-FM-3K	PenatMag with 3M RG-174 and FME-Female

Specifications subject to change without notice.


5 Little Balmer
Buckingham Industrial Park
Buckingham
MK18 1TF
UK

Tel: +44 (0)1280 824055
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com


EAD 
embedded antenna design ltd
Delivering Antenna Innovation

PentaMag | Multiband Magnetic Antenna

Return Loss



Outline Drawing



Specifications subject to change without notice.

5 Little Balmer
Buckingham Industrial Park
Buckingham
MK18 1TF
UK

Tel: +44 (0)1280 824055
Fax: +44 (0)1280 817179
Email: sales@ead-ltd.com
Web: www.ead-ltd.com

EAD
embedded antenna design ltd
Delivering Antenna Innovation